

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205443

Luminaire Tested: **LE\_6B50D010R EC6B30509727 6LBSLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205443  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B50D010R EC6B30509727 6LBSLI1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5145.0 lumens  
Efficiency: N/A  
Efficacy: 87.5 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 58.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205443

CATALOG NUMBER: LE\_6B50D010R EC6B30509727 6LBSLI1

### Luminous Intensity Polar Plot





TEST NUMBER: P205443

CATALOG NUMBER: LE\_6B50D010R EC6B30509727 6LBSLI1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89																			
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77																			
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68																			
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60																			
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53																			
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47																			
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43																			
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39																			
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36																			
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205443

CATALOG NUMBER: LE\_6B50D010R EC6B30509727 6LBSLI1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	299.2	5.8
10°-20°	761.6	14.8
20°-30°	971.3	18.9
30°-40°	1007.2	19.6
40°-50°	928.1	18.0
50°-60°	698.1	13.6
60°-70°	376.9	7.3
70°-80°	101.1	2.0
80°-90°	1.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2032.1	39.5
0°-40°	3039.3	59.1
0°-60°	4665.6	90.7
0°-90°	5145.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5145.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3247	
5°	3198	299
15°	2716	762
25°	2110	971
35°	1607	1007
45°	1208	928
55°	782	698
65°	377	377
75°	88	101
85°	0	1
90°	0	



TEST NUMBER: P205443

CATALOG NUMBER: LE\_6B50D010R EC6B30509727 6LBSLI1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3246.8
2.5°	3235.8
5°	3197.5
7.5°	3126.5
10°	3000.8
12.5°	2875.1
15°	2716.5
17.5°	2569.0
20°	2415.9
22.5°	2257.4
25°	2109.9
27.5°	1967.8
30°	1836.5
32.5°	1716.2
35°	1607.0
37.5°	1503.1
40°	1404.8
42.5°	1300.9
45°	1208.0
47.5°	1104.1
50°	1000.2
52.5°	891.0
55°	781.6
57.5°	672.2
60°	568.5
62.5°	470.1
65°	377.1
67.5°	289.8
70°	213.1
72.5°	147.6
75°	87.5
77.5°	38.2
80°	10.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)