

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204276

Luminaire Tested: **LE_6B20D010 EC6B10209727 6LBSWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204276
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B20D010 EC6B10209727 6LBSWH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1905.4 lumens
Efficiency: N/A
Efficacy: 91.6 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204276

CATALOG NUMBER: LE_6B20D010 EC6B10209727 6LBSWH1

Luminous Intensity Polar Plot





TEST NUMBER: P204276

CATALOG NUMBER: LE_6B20D010 EC6B10209727 6LBSWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89			
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67			
4	88	77	70	64	86	76	69	63	74	68	63	72	66	62	69	65	61	59			
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52			
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47			
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38			
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204276

CATALOG NUMBER: LE_6B20D010 EC6B10209727 6LBSWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.8	5.5
10°-20°	271.3	14.2
20°-30°	354.8	18.6
30°-40°	375.7	19.7
40°-50°	350.4	18.4
50°-60°	265.4	13.9
60°-70°	143.8	7.5
70°-80°	38.6	2.0
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	730.9	38.4
0°-40°	1106.6	58.1
0°-60°	1722.5	90.4
0°-90°	1905.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1905.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1136	
5°	1120	105
15°	970	271
25°	772	355
35°	600	376
45°	457	350
55°	298	265
65°	144	144
75°	33	39
85°	0	1
90°	0	



TEST NUMBER: P204276

CATALOG NUMBER: LE_6B20D010 EC6B10209727 6LBSWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1136.4
2.5°	1132.1
5°	1119.6
7.5°	1092.6
10°	1057.1
12.5°	1015.4
15°	969.5
17.5°	917.4
20°	871.5
22.5°	819.4
25°	771.5
27.5°	723.5
30°	677.6
32.5°	638.0
35°	600.5
37.5°	563.0
40°	527.5
42.5°	492.1
45°	456.6
47.5°	417.0
50°	377.4
52.5°	337.8
55°	298.1
57.5°	256.5
60°	216.9
62.5°	179.4
65°	143.9
67.5°	110.5
70°	81.4
72.5°	56.2
75°	33.4
77.5°	14.6
80°	4.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)