

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204719

Luminaire Tested: **LE_6B50D010R EC6B30508030 6LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204719
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B50D010R EC6B30508030 6LBPSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7256.5 lumens
Efficiency: N/A
Efficacy: 123.4 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204719

CATALOG NUMBER: LE_6B50D010R EC6B30508030 6LBPSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204719

CATALOG NUMBER: LE_6B50D010R EC6B30508030 6LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																												
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74																												
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63																												
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54																												
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47																												
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42																												
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37																												
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33																												
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30																												
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27																												

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204719

CATALOG NUMBER: LE_6B50D010R EC6B30508030 6LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	277.0	3.8
10°-20°	789.7	10.9
20°-30°	1189.2	16.4
30°-40°	1415.1	19.5
40°-50°	1412.5	19.5
50°-60°	1148.7	15.8
60°-70°	706.7	9.7
70°-80°	273.8	3.8
80°-90°	43.9	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2255.9	31.1
0°-40°	3671.0	50.6
0°-60°	6232.2	85.9
0°-90°	7256.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7256.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2924	
5°	2915	277
15°	2803	790
25°	2588	1189
35°	2266	1415
45°	1836	1413
55°	1286	1149
65°	709	707
75°	249	274
85°	34	44
90°	0	



TEST NUMBER: P204719

CATALOG NUMBER: LE_6B50D010R EC6B30508030 6LBPSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2923.6
2.5°	2928.0
5°	2915.1
7.5°	2897.9
10°	2876.4
12.5°	2837.8
15°	2803.2
17.5°	2751.8
20°	2695.8
22.5°	2644.2
25°	2588.4
27.5°	2510.9
30°	2433.5
32.5°	2360.5
35°	2265.9
37.5°	2162.6
40°	2068.1
42.5°	1952.0
45°	1835.9
47.5°	1711.2
50°	1577.9
52.5°	1440.4
55°	1285.5
57.5°	1135.1
60°	988.9
62.5°	847.0
65°	709.4
67.5°	580.4
70°	460.0
72.5°	348.2
75°	249.4
77.5°	163.4
80°	98.9
82.5°	60.2
85°	34.4
87.5°	17.2
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)