

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203236

Luminaire Tested: **LE\_6B20D010 EC6B10208030 6LBMH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203236  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B20D010 EC6B10208030 6LBMH1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W  
DL3-21.8 6 W DLE-22.46 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1862.1 lumens  
Efficiency: N/A  
Efficacy: 89.5 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203236

CATALOG NUMBER: LE\_6B20D010 EC6B10208030 6LBMH1

### Luminous Intensity Polar Plot





TEST NUMBER: P203236

CATALOG NUMBER: LE\_6B20D010 EC6B10208030 6LBMH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92																																				
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85																																				
3	101	94	88	84	99	92	88	84	90	86	82	87	84	81	85	82	80	78																																				
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72																																				
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66																																				
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61																																				
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																																				
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53																																				
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49																																				
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46																																				

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203236

CATALOG NUMBER: LE\_6B20D010 EC6B10208030 6LBMH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	168.5	9.0
10°-20°	435.9	23.4
20°-30°	564.8	30.3
30°-40°	419.3	22.5
40°-50°	177.0	9.5
50°-60°	62.9	3.4
60°-70°	24.2	1.3
70°-80°	8.4	0.5
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1169.2	62.8
0°-40°	1588.5	85.3
0°-60°	1828.4	98.2
0°-90°	1862.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1862.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1843	
5°	1803	168
15°	1556	436
25°	1252	565
35°	665	419
45°	218	177
55°	66	63
65°	24	24
75°	8	8
85°	0	1
90°	0	



TEST NUMBER: P203236

CATALOG NUMBER: LE\_6B20D010 EC6B10208030 6LBMH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1842.9
2.5°	1837.5
5°	1803.0
7.5°	1752.4
10°	1691.2
12.5°	1624.8
15°	1555.6
17.5°	1478.5
20°	1409.4
22.5°	1337.6
25°	1252.5
27.5°	1135.5
30°	997.2
32.5°	835.0
35°	664.8
37.5°	521.2
40°	396.2
42.5°	295.1
45°	218.0
47.5°	159.5
50°	117.0
52.5°	87.8
55°	66.5
57.5°	50.5
60°	39.9
62.5°	29.2
65°	23.9
67.5°	18.6
70°	13.2
72.5°	10.6
75°	8.0
77.5°	5.4
80°	2.6
82.5°	2.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)