

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205439

Luminaire Tested: **LE_6B50D010R EC6B30509030 6LBSLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205439
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B50D010R EC6B30509030 6LBSLI1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6151.6 lumens
Efficiency: N/A
Efficacy: 104.6 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205439

CATALOG NUMBER: LE_6B50D010R EC6B30509030 6LBSLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205439

CATALOG NUMBER: LE_6B50D010R EC6B30509030 6LBSLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89																			
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77																			
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68																			
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60																			
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53																			
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47																			
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43																			
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39																			
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36																			
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205439

CATALOG NUMBER: LE_6B50D010R EC6B30509030 6LBSLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	357.7	5.8
10°-20°	910.7	14.8
20°-30°	1161.3	18.9
30°-40°	1204.3	19.6
40°-50°	1109.7	18.0
50°-60°	834.7	13.6
60°-70°	450.6	7.3
70°-80°	120.9	2.0
80°-90°	1.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2429.7	39.5
0°-40°	3634.0	59.1
0°-60°	5578.4	90.7
0°-90°	6151.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6151.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3882	
5°	3823	358
15°	3248	911
25°	2523	1161
35°	1921	1204
45°	1444	1110
55°	934	835
65°	451	451
75°	105	121
85°	0	2
90°	0	



TEST NUMBER: P205439

CATALOG NUMBER: LE_6B50D010R EC6B30509030 6LBSLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3882.0
2.5°	3868.9
5°	3823.1
7.5°	3738.1
10°	3587.9
12.5°	3437.6
15°	3248.0
17.5°	3071.6
20°	2888.6
22.5°	2699.1
25°	2522.6
27.5°	2352.8
30°	2195.9
32.5°	2052.1
35°	1921.4
37.5°	1797.2
40°	1679.6
42.5°	1555.4
45°	1444.2
47.5°	1320.1
50°	1196.0
52.5°	1065.2
55°	934.5
57.5°	803.9
60°	679.6
62.5°	562.0
65°	450.9
67.5°	346.4
70°	254.9
72.5°	176.5
75°	104.6
77.5°	45.8
80°	13.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)