

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204680

Luminaire Tested: **LE_6B20D010 EC6B10208030 6LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204680
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B20D010 EC6B10208030 6LBPSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2859.2 lumens
Efficiency: N/A
Efficacy: 137.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204680

CATALOG NUMBER: LE_6B20D010 EC6B10208030 6LBPSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204680

CATALOG NUMBER: LE_6B20D010 EC6B10208030 6LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86				86
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74				74
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63				63
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54				54
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47				47
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42				42
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37				37
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33				33
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30				30
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204680

CATALOG NUMBER: LE_6B20D010 EC6B10208030 6LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.2	3.8
10°-20°	311.1	10.9
20°-30°	468.6	16.4
30°-40°	557.6	19.5
40°-50°	556.6	19.5
50°-60°	452.6	15.8
60°-70°	278.5	9.7
70°-80°	107.9	3.8
80°-90°	17.3	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	888.9	31.1
0°-40°	1446.4	50.6
0°-60°	2455.6	85.9
0°-90°	2859.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2859.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1152	
5°	1149	109
15°	1104	311
25°	1020	469
35°	893	558
45°	723	557
55°	506	453
65°	280	278
75°	98	108
85°	14	17
90°	0	



TEST NUMBER: P204680

CATALOG NUMBER: LE_6B20D010 EC6B10208030 6LBPSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1152.0
2.5°	1153.6
5°	1148.6
7.5°	1141.8
10°	1133.4
12.5°	1118.1
15°	1104.5
17.5°	1084.2
20°	1062.1
22.5°	1041.9
25°	1019.9
27.5°	989.4
30°	958.9
32.5°	930.0
35°	892.8
37.5°	852.1
40°	814.9
42.5°	769.1
45°	723.4
47.5°	674.2
50°	621.8
52.5°	567.5
55°	506.5
57.5°	447.2
60°	389.6
62.5°	333.8
65°	279.5
67.5°	228.8
70°	181.2
72.5°	137.2
75°	98.2
77.5°	64.4
80°	39.0
82.5°	23.8
85°	13.5
87.5°	6.8
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)