

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204621

Luminaire Tested: **LE_6B50D010R EC6B30509030 6LBSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204621
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B50D010R EC6B30509030 6LBSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6197.3 lumens
Efficiency: N/A
Efficacy: 105.4 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204621

CATALOG NUMBER: LE_6B50D010R EC6B30509030 6LBSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204621

CATALOG NUMBER: LE_6B50D010R EC6B30509030 6LBSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86				86
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74				74
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63				63
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54				54
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47				47
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42				42
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37				37
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33				33
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30				30
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204621

CATALOG NUMBER: LE_6B50D010R EC6B30509030 6LBSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	236.6	3.8
10°-20°	674.4	10.9
20°-30°	1015.6	16.4
30°-40°	1208.5	19.5
40°-50°	1206.3	19.5
50°-60°	981.0	15.8
60°-70°	603.6	9.7
70°-80°	233.8	3.8
80°-90°	37.5	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1926.6	31.1
0°-40°	3135.1	50.6
0°-60°	5322.4	85.9
0°-90°	6197.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6197.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2497	
5°	2490	237
15°	2394	674
25°	2210	1016
35°	1935	1209
45°	1568	1206
55°	1098	981
65°	606	604
75°	213	234
85°	29	37
90°	0	



TEST NUMBER: P204621

CATALOG NUMBER: LE_6B50D010R EC6B30509030 6LBSMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	2496.9
2.5°	2500.5
5°	2489.5
7.5°	2474.9
10°	2456.5
12.5°	2423.5
15°	2394.1
17.5°	2350.0
20°	2302.2
22.5°	2258.2
25°	2210.5
27.5°	2144.4
30°	2078.2
32.5°	2015.9
35°	1935.1
37.5°	1847.0
40°	1766.1
42.5°	1667.0
45°	1567.9
47.5°	1461.4
50°	1347.6
52.5°	1230.1
55°	1097.9
57.5°	969.4
60°	844.5
62.5°	723.4
65°	605.9
67.5°	495.8
70°	392.9
72.5°	297.4
75°	213.0
77.5°	139.5
80°	84.5
82.5°	51.4
85°	29.4
87.5°	14.8
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)