

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204369

Luminaire Tested: **LE_6B20D010 EC6B10208030 6LBSGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204369
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B20D010 EC6B10208030 6LBSGPH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2434.3 lumens
Efficiency: N/A
Efficacy: 117.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204369

CATALOG NUMBER: LE_6B20D010 EC6B10208030 6LBSGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P204369

CATALOG NUMBER: LE_6B20D010 EC6B10208030 6LBSGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	91	90	88			88
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76			76
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66			66
4	87	76	68	62	85	75	67	62	72	66	61	70	65	60	68	63	59	57			57
5	80	68	60	54	78	67	60	54	65	59	53	63	58	53	62	56	52	50			50
6	74	62	54	48	73	61	53	48	59	52	47	58	52	47	56	51	47	45			45
7	69	57	48	43	68	56	48	43	54	47	42	53	47	42	52	46	42	40			40
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36			36
9	60	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	32			32
10	57	44	37	32	56	44	36	32	43	36	31	42	36	31	41	35	31	30			30

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204369

CATALOG NUMBER: LE_6B20D010 EC6B10208030 6LBSGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.4	4.4
10°-20°	298.8	12.3
20°-30°	435.8	17.9
30°-40°	497.0	20.4
40°-50°	476.7	19.6
50°-60°	365.1	15.0
60°-70°	200.4	8.2
70°-80°	53.3	2.2
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	841.0	34.5
0°-40°	1338.0	55.0
0°-60°	2179.8	89.5
0°-90°	2434.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2434.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1131	
5°	1122	106
15°	1060	299
25°	946	436
35°	795	497
45°	619	477
55°	409	365
65°	202	200
75°	47	53
85°	0	1
90°	0	



TEST NUMBER: P204369

CATALOG NUMBER: LE_6B20D010 EC6B10208030 6LBSGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1130.6
2.5°	1127.6
5°	1121.9
7.5°	1113.0
10°	1101.4
12.5°	1080.9
15°	1060.5
17.5°	1037.1
20°	1010.8
22.5°	978.6
25°	946.5
27.5°	914.4
30°	873.5
32.5°	835.5
35°	794.6
37.5°	753.8
40°	712.9
42.5°	669.0
45°	619.4
47.5°	569.6
50°	517.1
52.5°	461.6
55°	409.0
57.5°	356.4
60°	300.9
62.5°	248.4
65°	201.6
67.5°	154.9
70°	113.9
72.5°	76.0
75°	46.8
77.5°	20.5
80°	5.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)