

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P252819

Luminaire Tested: **LE_6B50D010R EC6B30508035 6LBBA1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P252819
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1712-453-2)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B50D010R EC6B30508035 6LBBA1MW
Description: PORTFOLIO 6 INCH BAFFLE RECESSED DOWNLIGHT, WITH MATTE WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8718.8 lumens
Efficiency: N/A
Efficacy: 148.3 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 58.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P252819

CATALOG NUMBER: LE_6B50D010R EC6B30508035 6LBBA1MW

Luminous Intensity Polar Plot





TEST NUMBER: P252819

CATALOG NUMBER: LE_6B50D010R EC6B30508035 6LBBA1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88			
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78			
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69			
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	68	64	62			
5	84	73	65	60	82	72	65	60	70	64	59	68	63	58	66	62	58	56			
6	78	67	60	54	77	66	59	54	65	58	54	63	57	53	62	57	53	51			
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	47			
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	53	48	44	43			
9	65	54	46	42	64	53	46	42	52	46	41	51	45	41	50	45	41	39			
10	62	50	43	39	61	50	43	39	49	43	38	48	42	38	47	42	38	37			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	390139
5°	386554
10°	378039
15°	366037
20°	351262
25°	329749
30°	285333
35°	222167
40°	168866
45°	131624
50°	109170
55°	97990
60°	89223
65°	82311
70°	75633
75°	70076
80°	63344
85°	58013



TEST NUMBER: P252819

CATALOG NUMBER: LE_6B50D010R EC6B30508035 6LBBA1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	557.1	6.4
10°-20°	1522.7	17.5
20°-30°	2073.8	23.8
30°-40°	1754.9	20.1
40°-50°	1125.8	12.9
50°-60°	774.7	8.9
60°-70°	529.2	6.1
70°-80°	294.5	3.4
80°-90°	86.2	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4153.6	47.6
0°-40°	5908.5	67.8
0°-60°	7808.9	89.6
0°-90°	8718.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8718.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5980	
5°	5902	557
15°	5419	1523
25°	4581	2074
35°	2790	1755
45°	1427	1126
55°	862	775
65°	533	529
75°	278	294
85°	78	86
90°	0	



TEST NUMBER: P252819

CATALOG NUMBER: LE_6B50D010R EC6B30508035 6LBBA1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	5980.0
2.5°	5957.2
5°	5902.5
7.5°	5816.0
10°	5706.5
12.5°	5569.8
15°	5419.4
17.5°	5246.2
20°	5059.4
22.5°	4849.6
25°	4580.8
27.5°	4216.1
30°	3787.6
32.5°	3295.4
35°	2789.5
37.5°	2347.4
40°	1982.8
42.5°	1677.4
45°	1426.6
47.5°	1230.6
50°	1075.6
52.5°	957.1
55°	861.5
57.5°	770.2
60°	683.8
62.5°	606.2
65°	533.2
67.5°	460.4
70°	396.5
72.5°	332.8
75°	278.0
77.5°	223.4
80°	168.6
82.5°	123.1
85°	77.5
87.5°	31.9
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)