

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203276

Luminaire Tested: **LE\_6B50D010R EC6B30508035 6LBMH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203276  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B50D010R EC6B30508035 6LBMH1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5008.8 lumens  
Efficiency: N/A  
Efficacy: 85.2 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 58.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203276

CATALOG NUMBER: LE\_6B50D010R EC6B30508035 6LBMH1

### Luminous Intensity Polar Plot





TEST NUMBER: P203276

CATALOG NUMBER: LE\_6B50D010R EC6B30508035 6LBMH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    |    |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |
| 1   | 113 | 110 | 107 | 105 | 111 | 108 | 105 | 103 | 104 | 102 | 100 | 100 | 99  | 97  | 97  | 95  | 94  | 92  |    |    |
| 2   | 107 | 102 | 97  | 93  | 105 | 100 | 96  | 92  | 97  | 93  | 90  | 94  | 91  | 88  | 91  | 89  | 87  | 85  |    |    |
| 3   | 101 | 94  | 88  | 84  | 99  | 92  | 87  | 84  | 90  | 86  | 82  | 87  | 84  | 81  | 85  | 82  | 80  | 78  |    |    |
| 4   | 95  | 87  | 81  | 76  | 93  | 86  | 80  | 76  | 84  | 79  | 75  | 82  | 78  | 74  | 80  | 76  | 73  | 72  |    |    |
| 5   | 90  | 81  | 75  | 70  | 88  | 80  | 74  | 70  | 78  | 73  | 69  | 76  | 72  | 68  | 75  | 71  | 68  | 66  |    |    |
| 6   | 85  | 75  | 69  | 64  | 83  | 75  | 69  | 64  | 73  | 68  | 64  | 72  | 67  | 63  | 70  | 66  | 63  | 61  |    |    |
| 7   | 80  | 70  | 64  | 59  | 79  | 70  | 64  | 59  | 68  | 63  | 59  | 67  | 62  | 59  | 66  | 62  | 58  | 57  |    |    |
| 8   | 76  | 66  | 60  | 55  | 75  | 65  | 59  | 55  | 64  | 59  | 55  | 63  | 58  | 55  | 62  | 58  | 54  | 53  |    |    |
| 9   | 72  | 62  | 56  | 51  | 71  | 61  | 55  | 51  | 60  | 55  | 51  | 60  | 55  | 51  | 59  | 54  | 51  | 49  |    |    |
| 10  | 69  | 58  | 52  | 48  | 68  | 58  | 52  | 48  | 57  | 52  | 48  | 56  | 51  | 48  | 55  | 51  | 48  | 46  |    |    |

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203276

CATALOG NUMBER: LE\_6B50D010R EC6B30508035 6LBMH1

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 453.2  | 9.0       |
| 10°-20°   | 1172.5 | 23.4      |
| 20°-30°   | 1519.2 | 30.3      |
| 30°-40°   | 1127.9 | 22.5      |
| 40°-50°   | 476.1  | 9.5       |
| 50°-60°   | 169.1  | 3.4       |
| 60°-70°   | 65.2   | 1.3       |
| 70°-80°   | 22.6   | 0.5       |
| 80°-90°   | 2.9    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 3145.0 | 62.8      |
| 0°-40°    | 4272.9 | 85.3      |
| 0°-60°    | 4918.1 | 98.2      |
| 0°-90°    | 5008.8 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 5008.8 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 4957 |      |
| 5°  | 4850 | 453  |
| 15° | 4184 | 1172 |
| 25° | 3369 | 1519 |
| 35° | 1788 | 1128 |
| 45° | 586  | 476  |
| 55° | 179  | 169  |
| 65° | 64   | 65   |
| 75° | 22   | 23   |
| 85° | 0    | 3    |
| 90° | 0    |      |



TEST NUMBER: P203276

CATALOG NUMBER: LE\_6B50D010R EC6B30508035 6LBMH1

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 4956.9 |
| 2.5°  | 4942.6 |
| 5°    | 4849.6 |
| 7.5°  | 4713.8 |
| 10°   | 4549.1 |
| 12.5° | 4370.4 |
| 15°   | 4184.4 |
| 17.5° | 3977.0 |
| 20°   | 3791.0 |
| 22.5° | 3597.9 |
| 25°   | 3369.0 |
| 27.5° | 3054.2 |
| 30°   | 2682.2 |
| 32.5° | 2246.0 |
| 35°   | 1788.2 |
| 37.5° | 1402.0 |
| 40°   | 1065.8 |
| 42.5° | 794.0  |
| 45°   | 586.5  |
| 47.5° | 429.1  |
| 50°   | 314.8  |
| 52.5° | 236.0  |
| 55°   | 178.9  |
| 57.5° | 135.9  |
| 60°   | 107.2  |
| 62.5° | 78.6   |
| 65°   | 64.4   |
| 67.5° | 50.1   |
| 70°   | 35.8   |
| 72.5° | 28.6   |
| 75°   | 21.5   |
| 77.5° | 14.2   |
| 80°   | 7.1    |
| 82.5° | 7.1    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)