

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204892

Luminaire Tested: **LE_6B20D010 EC6B10209030 6LBCSMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204892
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B20D010 EC6B10209030 6LBCSMB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2019.5 lumens
Efficiency: N/A
Efficacy: 97.1 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204892

CATALOG NUMBER: LE_6B20D010 EC6B10209030 6LBCSMB1

Luminous Intensity Polar Plot





TEST NUMBER: P204892

CATALOG NUMBER: LE_6B20D010 EC6B10209030 6LBCSMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88			88
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75			75
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65			65
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56			56
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49			49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43			43
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39			39
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35			35
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31			31
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28			28

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204892

CATALOG NUMBER: LE_6B20D010 EC6B10209030 6LBCSMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.7	4.0
10°-20°	229.8	11.4
20°-30°	345.4	17.1
30°-40°	409.9	20.3
40°-50°	405.6	20.1
50°-60°	318.6	15.8
60°-70°	178.6	8.8
70°-80°	50.2	2.5
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	655.9	32.5
0°-40°	1065.7	52.8
0°-60°	1789.9	88.6
0°-90°	2019.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2019.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	853	
5°	851	81
15°	815	230
25°	750	345
35°	657	410
45°	528	406
55°	359	319
65°	178	179
75°	43	50
85°	0	1
90°	0	



TEST NUMBER: P204892

CATALOG NUMBER: LE_6B20D010 EC6B10209030 6LBCSMB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	852.8
2.5°	849.9
5°	851.2
7.5°	844.0
10°	835.4
12.5°	825.2
15°	815.1
17.5°	802.1
20°	784.8
22.5°	767.4
25°	750.0
27.5°	731.1
30°	706.5
32.5°	681.9
35°	657.2
37.5°	628.4
40°	595.0
42.5°	563.1
45°	528.4
47.5°	489.4
50°	448.8
52.5°	402.5
55°	359.0
57.5°	309.9
60°	263.5
62.5°	221.5
65°	178.1
67.5°	140.4
70°	104.2
72.5°	71.0
75°	43.4
77.5°	21.8
80°	5.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)