

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204375

Luminaire Tested: **LE_6B20D010 EC6B10209030 6LBSGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204375
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B20D010 EC6B10209030 6LBSGPH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2079.2 lumens
Efficiency: N/A
Efficacy: 100.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204375

CATALOG NUMBER: LE_6B20D010 EC6B10209030 6LBSGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P204375

CATALOG NUMBER: LE_6B20D010 EC6B10209030 6LBSGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	91	90	88
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66
4	87	76	68	62	85	75	67	62	72	66	61	70	65	60	68	63	59	57
5	80	68	60	54	78	67	60	54	65	59	53	63	58	53	62	56	52	50
6	74	62	54	48	73	61	53	48	59	52	47	58	52	47	56	51	47	45
7	69	57	48	43	68	56	48	43	54	47	42	53	47	42	52	46	42	40
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36
9	60	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	32
10	57	44	37	32	56	44	36	32	43	36	31	42	36	31	41	35	31	30

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204375

CATALOG NUMBER: LE_6B20D010 EC6B10209030 6LBSGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.9	4.4
10°-20°	255.2	12.3
20°-30°	372.2	17.9
30°-40°	424.5	20.4
40°-50°	407.2	19.6
50°-60°	311.8	15.0
60°-70°	171.1	8.2
70°-80°	45.5	2.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	718.4	34.6
0°-40°	1142.9	55.0
0°-60°	1861.9	89.5
0°-90°	2079.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2079.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	966	
5°	958	91
15°	906	255
25°	808	372
35°	679	424
45°	529	407
55°	349	312
65°	172	171
75°	40	46
85°	0	1
90°	0	



TEST NUMBER: P204375

CATALOG NUMBER: LE_6B20D010 EC6B10209030 6LBSGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	965.8
2.5°	963.2
5°	958.2
7.5°	950.8
10°	940.8
12.5°	923.2
15°	905.9
17.5°	885.9
20°	863.4
22.5°	836.0
25°	808.5
27.5°	781.0
30°	746.1
32.5°	713.6
35°	678.8
37.5°	643.8
40°	608.9
42.5°	571.4
45°	529.0
47.5°	486.6
50°	441.6
52.5°	394.2
55°	349.4
57.5°	304.4
60°	257.0
62.5°	212.1
65°	172.1
67.5°	132.2
70°	97.4
72.5°	64.9
75°	39.9
77.5°	17.5
80°	5.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)