

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203139

Luminaire Tested: **LE_6B20D010 EC6B10209030 6LBWMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203139
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B20D010 EC6B10209030 6LBWMW1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2056.8 lumens
Efficiency: N/A
Efficacy: 98.9 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.15
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203139

CATALOG NUMBER: LE_6B20D010 EC6B10209030 6LBWMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203139

CATALOG NUMBER: LE_6B20D010 EC6B10209030 6LBWMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77			
3	95	86	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68			
4	89	78	71	65	86	77	70	65	75	69	64	72	67	63	70	66	62	60			
5	82	71	64	58	80	70	63	58	68	62	57	66	61	56	65	60	56	54			
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	49			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			
8	67	55	48	42	66	55	47	42	53	47	42	52	46	42	51	46	42	40			
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37			
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203139

CATALOG NUMBER: LE_6B20D010 EC6B10209030 6LBWMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.8	5.3
10°-20°	305.0	14.8
20°-30°	439.5	21.4
30°-40°	456.3	22.2
40°-50°	337.4	16.4
50°-60°	201.5	9.8
60°-70°	122.4	6.0
70°-80°	67.1	3.3
80°-90°	18.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	853.3	41.5
0°-40°	1309.7	63.7
0°-60°	1848.6	89.9
0°-90°	2056.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2056.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1155	
5°	1148	109
15°	1083	305
25°	958	440
35°	736	456
45°	434	337
55°	220	202
65°	122	122
75°	62	67
85°	15	19
90°	0	



TEST NUMBER: P203139

CATALOG NUMBER: LE_6B20D010 EC6B10209030 6LBWMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1155.0
2.5°	1155.0
5°	1147.5
7.5°	1137.6
10°	1122.6
12.5°	1105.1
15°	1082.6
17.5°	1057.8
20°	1032.8
22.5°	997.9
25°	958.0
27.5°	915.5
30°	860.6
32.5°	805.8
35°	735.9
37.5°	663.6
40°	583.8
42.5°	506.4
45°	434.1
47.5°	369.2
50°	311.9
52.5°	262.0
55°	219.5
57.5°	187.1
60°	159.6
62.5°	139.8
65°	122.2
67.5°	107.2
70°	92.2
72.5°	77.4
75°	62.4
77.5°	49.9
80°	37.4
82.5°	27.5
85°	15.0
87.5°	7.5
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)