

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205538

Luminaire Tested: **LE\_6B50D010R EC6B30508040 6LBMGPH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205538  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B50D010R EC6B30508040 6LBMGPH1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3861.5 lumens  
Efficiency: N/A  
Efficacy: 65.7 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 58.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205538

CATALOG NUMBER: LE\_6B50D010R EC6B30508040 6LBMGPH1

### Luminous Intensity Polar Plot





TEST NUMBER: P205538

CATALOG NUMBER: LE\_6B50D010R EC6B30508040 6LBMGPH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93																			
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86																			
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79																			
4	96	88	82	78	94	87	82	77	85	80	77	83	79	76	81	78	75	73																			
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68																			
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63																			
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59																			
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55																			
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51																			
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	53	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205538

CATALOG NUMBER: LE\_6B50D010R EC6B30508040 6LBMGPH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	369.6	9.6
10°-20°	959.2	24.8
20°-30°	1222.1	31.6
30°-40°	863.7	22.4
40°-50°	315.3	8.2
50°-60°	87.4	2.3
60°-70°	31.7	0.8
70°-80°	11.3	0.3
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2551.0	66.1
0°-40°	3414.7	88.4
0°-60°	3817.4	98.9
0°-90°	3861.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3861.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4024	
5°	3954	370
15°	3416	959
25°	2714	1222
35°	1372	864
45°	382	315
55°	94	87
65°	31	32
75°	8	11
85°	0	1
90°	0	



TEST NUMBER: P205538

CATALOG NUMBER: LE\_6B50D010R EC6B30508040 6LBMGPH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4023.9
2.5°	4008.2
5°	3953.6
7.5°	3844.5
10°	3727.5
12.5°	3571.5
15°	3415.6
17.5°	3259.6
20°	3103.6
22.5°	2916.5
25°	2713.8
27.5°	2433.0
30°	2121.1
32.5°	1746.8
35°	1372.5
37.5°	1045.0
40°	764.2
42.5°	553.6
45°	382.1
47.5°	257.4
50°	171.5
52.5°	117.0
55°	93.6
57.5°	70.1
60°	54.6
62.5°	39.0
65°	31.2
67.5°	23.4
70°	15.6
72.5°	15.6
75°	7.8
77.5°	7.8
80°	7.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)