

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203556

Luminaire Tested: **LE_6B20D010 EC6B10209730 6LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203556
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B20D010 EC6B10209730 6LBMMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1525.1 lumens
Efficiency: N/A
Efficacy: 73.3 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203556

CATALOG NUMBER: LE_6B20D010 EC6B10209730 6LBMMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203556

CATALOG NUMBER: LE_6B20D010 EC6B10209730 6LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58			
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53			
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48			
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41			
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203556

CATALOG NUMBER: LE_6B20D010 EC6B10209730 6LBMMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.1	6.9
10°-20°	281.6	18.5
20°-30°	378.1	24.8
30°-40°	310.1	20.3
40°-50°	186.3	12.2
50°-60°	123.8	8.1
60°-70°	82.9	5.4
70°-80°	44.6	2.9
80°-90°	12.6	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	764.8	50.1
0°-40°	1074.9	70.5
0°-60°	1385.0	90.8
0°-90°	1525.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1525.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1138	
5°	1119	105
15°	1003	282
25°	833	378
35°	492	310
45°	236	186
55°	137	124
65°	84	83
75°	42	45
85°	10	13
90°	0	



TEST NUMBER: P203556

CATALOG NUMBER: LE_6B20D010 EC6B10209730 6LBMMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1138.0
2.5°	1129.6
5°	1119.0
7.5°	1095.9
10°	1068.6
12.5°	1034.9
15°	1003.4
17.5°	965.5
20°	927.6
22.5°	885.6
25°	833.0
27.5°	769.9
30°	685.8
32.5°	591.1
35°	492.2
37.5°	408.1
40°	336.5
42.5°	279.8
45°	235.6
47.5°	199.9
50°	174.6
52.5°	153.5
55°	136.8
57.5°	122.0
60°	109.4
62.5°	94.6
65°	84.1
67.5°	71.5
70°	61.0
72.5°	50.5
75°	42.1
77.5°	33.6
80°	25.2
82.5°	18.9
85°	10.5
87.5°	4.2
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)