

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202629

Luminaire Tested: **LE_6B20D010 EC6B10209730 6LBMWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202629
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B20D010 EC6B10209730 6LBMWMH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1491.8 lumens
Efficiency: N/A
Efficacy: 71.7 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.89
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202629

CATALOG NUMBER: LE_6B20D010 EC6B10209730 6LBMWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P202629

CATALOG NUMBER: LE_6B20D010 EC6B10209730 6LBMWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																					
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																																				
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86																																				
3	102	95	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																																				
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74																																				
5	92	83	77	73	90	82	77	73	80	76	72	79	75	71	77	74	71	69																																				
6	87	78	72	67	85	77	71	67	76	71	67	74	70	66	73	69	66	64																																				
7	83	73	67	63	81	72	67	63	71	66	62	70	65	62	69	65	62	60																																				
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	58	56																																				
9	75	65	59	55	73	64	59	55	63	58	54	62	58	54	62	57	54	53																																				
10	71	61	55	51	70	61	55	51	60	55	51	59	54	51	58	54	51	50																																				

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202629

CATALOG NUMBER: LE_6B20D010 EC6B10209730 6LBMWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.3	10.2
10°-20°	390.9	26.2
20°-30°	480.1	32.2
30°-40°	329.2	22.1
40°-50°	105.8	7.1
50°-60°	21.5	1.4
60°-70°	8.4	0.6
70°-80°	3.1	0.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1023.3	68.6
0°-40°	1352.5	90.7
0°-60°	1479.8	99.2
0°-90°	1491.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1491.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1659	
5°	1628	152
15°	1398	391
25°	1059	480
35°	525	329
45°	125	106
55°	22	21
65°	9	8
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P202629

CATALOG NUMBER: LE_6B20D010 EC6B10209730 6LBMWMH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1659.1
2.5°	1649.0
5°	1627.5
7.5°	1587.0
10°	1532.5
12.5°	1465.5
15°	1398.4
17.5°	1323.8
20°	1241.5
22.5°	1155.4
25°	1059.2
27.5°	952.9
30°	818.8
32.5°	670.8
35°	525.2
37.5°	392.2
40°	282.2
42.5°	192.4
45°	125.2
47.5°	77.2
50°	46.9
52.5°	29.1
55°	21.5
57.5°	16.5
60°	12.6
62.5°	10.1
65°	8.9
67.5°	6.4
70°	5.0
72.5°	3.8
75°	2.5
77.5°	2.5
80°	1.2
82.5°	1.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)