

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205130

Luminaire Tested: **LE_6B50D010R EC6B30508040 6LBMLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205130
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B50D010R EC6B30508040 6LBML1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6192.6 lumens
Efficiency: N/A
Efficacy: 105.3 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205130

CATALOG NUMBER: LE_6B50D010R EC6B30508040 6LBML11

Luminous Intensity Polar Plot





TEST NUMBER: P205130

CATALOG NUMBER: LE_6B50D010R EC6B30508040 6LBML11

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																					
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																			
	1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94																																			
	2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88																																			
	3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82																																			
	4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76																																			
	5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71																																			
	6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67																																			
	7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63																																			
	8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59																																			
	9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																																			
	10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52																																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205130

CATALOG NUMBER: LE_6B50D010R EC6B30508040 6LBML11

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	713.9	11.5
10°-20°	1777.4	28.7
20°-30°	2066.2	33.4
30°-40°	1265.3	20.4
40°-50°	314.2	5.1
50°-60°	36.8	0.6
60°-70°	13.7	0.2
70°-80°	5.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4557.5	73.6
0°-40°	5822.8	94.0
0°-60°	6173.7	99.7
0°-90°	6192.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6192.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7750	
5°	7647	714
15°	6379	1777
25°	4572	2066
35°	1981	1265
45°	349	314
55°	32	37
65°	16	14
75°	8	5
85°	0	0
90°	0	



TEST NUMBER: P205130

CATALOG NUMBER: LE_6B50D010R EC6B30508040 6LBML11

CANDELA DISTRIBUTION (FULL):

	0°
0°	7749.9
2.5°	7741.9
5°	7646.8
7.5°	7440.8
10°	7163.4
12.5°	6798.9
15°	6379.0
17.5°	5927.2
20°	5483.5
22.5°	5039.8
25°	4572.2
27.5°	4033.4
30°	3415.2
32.5°	2694.2
35°	1981.0
37.5°	1394.6
40°	950.9
42.5°	594.2
45°	348.6
47.5°	198.1
50°	103.0
52.5°	47.5
55°	31.8
57.5°	23.8
60°	23.8
62.5°	15.9
65°	15.9
67.5°	7.9
70°	7.9
72.5°	7.9
75°	7.9
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)