

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203762

Luminaire Tested: **LE\_6B20D010 EC6B10209730 6LBNWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203762  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B20D010 EC6B10209730 6LBNWH1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
NARROW DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W  
DL3-21.8 6 W DLE-22.46 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1281.0 lumens  
Efficiency: N/A  
Efficacy: 61.6 lumens/watt  
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.64  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203762

CATALOG NUMBER: LE\_6B20D010 EC6B10209730 6LBNWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P203762

CATALOG NUMBER: LE\_6B20D010 EC6B10209730 6LBNWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94			
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89			
3	104	98	93	90	102	97	92	89	94	91	88	92	89	86	89	87	85	83			
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	79			
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74			
6	91	82	77	73	89	82	76	73	80	76	72	79	75	72	78	74	71	70			
7	87	78	73	69	85	77	72	69	76	72	68	75	71	68	74	70	67	66			
8	83	74	69	65	82	74	68	65	73	68	65	72	67	64	71	67	64	63			
9	79	71	65	62	78	70	65	61	69	65	61	68	64	61	68	64	61	60			
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203762

CATALOG NUMBER: LE\_6B20D010 EC6B10209730 6LBNWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	212.9	16.6
10°-20°	409.1	31.9
20°-30°	371.9	29.0
30°-40°	225.4	17.6
40°-50°	51.3	4.0
50°-60°	6.6	0.5
60°-70°	2.9	0.2
70°-80°	0.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	994.0	77.6
0°-40°	1219.4	95.2
0°-60°	1277.3	99.7
0°-90°	1281.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1281.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2515	
5°	2371	213
15°	1473	409
25°	806	372
35°	358	225
45°	57	51
55°	6	7
65°	2	3
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P203762

CATALOG NUMBER: LE\_6B20D010 EC6B10209730 6LBNWH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2515.1
2.5°	2484.6
5°	2371.4
7.5°	2188.2
10°	1955.0
12.5°	1713.1
15°	1473.4
17.5°	1255.4
20°	1072.4
22.5°	924.1
25°	806.4
27.5°	701.8
30°	599.4
32.5°	479.5
35°	357.5
37.5°	250.6
40°	165.6
42.5°	102.5
45°	56.6
47.5°	26.1
50°	10.9
52.5°	8.8
55°	6.5
57.5°	6.5
60°	4.4
62.5°	4.4
65°	2.1
67.5°	2.1
70°	2.1
72.5°	2.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)