

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203586

Luminaire Tested: **LE_6B50D010R EC6B30508040 6LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203586
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B50D010R EC6B30508040 6LBMMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5550.4 lumens
Efficiency: N/A
Efficacy: 94.4 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203586

CATALOG NUMBER: LE_6B50D010R EC6B30508040 6LBMMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203586

CATALOG NUMBER: LE_6B50D010R EC6B30508040 6LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89		
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79		
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71		
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64		
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58		
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53		
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48		
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44		
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41		
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203586

CATALOG NUMBER: LE_6B50D010R EC6B30508040 6LBMMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	382.6	6.9
10°-20°	1024.8	18.5
20°-30°	1376.0	24.8
30°-40°	1128.7	20.3
40°-50°	677.8	12.2
50°-60°	450.4	8.1
60°-70°	301.9	5.4
70°-80°	162.5	2.9
80°-90°	45.8	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2783.3	50.1
0°-40°	3912.0	70.5
0°-60°	5040.2	90.8
0°-90°	5550.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5550.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4142	
5°	4073	383
15°	3652	1025
25°	3032	1376
35°	1791	1129
45°	857	678
55°	498	450
65°	306	302
75°	153	163
85°	38	46
90°	0	



TEST NUMBER: P203586

CATALOG NUMBER: LE_6B50D010R EC6B30508040 6LBMMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	4141.5
2.5°	4110.9
5°	4072.6
7.5°	3988.4
10°	3888.9
12.5°	3766.4
15°	3651.5
17.5°	3513.8
20°	3376.0
22.5°	3222.9
25°	3031.5
27.5°	2801.8
30°	2495.6
32.5°	2151.1
35°	1791.4
37.5°	1485.1
40°	1224.9
42.5°	1018.1
45°	857.4
47.5°	727.2
50°	635.4
52.5°	558.9
55°	497.6
57.5°	444.0
60°	398.1
62.5°	344.5
65°	306.2
67.5°	260.2
70°	222.0
72.5°	183.8
75°	153.1
77.5°	122.5
80°	91.9
82.5°	68.9
85°	38.2
87.5°	15.2
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)