

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204410

Luminaire Tested: **LE_6B50D010R EC6B30508040 6LBSGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204410
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B50D010R EC6B30508040 6LBSGPH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6612.9 lumens
Efficiency: N/A
Efficacy: 112.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204410

CATALOG NUMBER: LE_6B50D010R EC6B30508040 6LBSGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P204410

CATALOG NUMBER: LE_6B50D010R EC6B30508040 6LBSGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	91	90	88			
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76			
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66			
4	87	76	68	62	85	75	67	62	72	66	61	70	65	60	68	63	59	57			
5	80	68	60	54	78	67	60	54	65	59	53	63	58	53	62	56	52	50			
6	74	62	54	48	73	61	53	48	59	52	47	58	52	47	56	51	47	45			
7	69	57	48	43	68	56	48	43	54	47	42	53	47	42	52	46	42	40			
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36			
9	60	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	32			
10	57	44	37	32	56	44	36	32	43	36	31	42	36	31	41	35	31	30			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204410

CATALOG NUMBER: LE_6B50D010R EC6B30508040 6LBSGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	289.2	4.4
10°-20°	811.7	12.3
20°-30°	1183.9	17.9
30°-40°	1350.1	20.4
40°-50°	1295.1	19.6
50°-60°	991.8	15.0
60°-70°	544.3	8.2
70°-80°	144.7	2.2
80°-90°	2.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2284.8	34.6
0°-40°	3634.8	55.0
0°-60°	5921.7	89.5
0°-90°	6612.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6612.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3071	
5°	3048	289
15°	2881	812
25°	2571	1184
35°	2159	1350
45°	1682	1295
55°	1111	992
65°	548	544
75°	127	145
85°	0	2
90°	0	



TEST NUMBER: P204410

CATALOG NUMBER: LE_6B50D010R EC6B30508040 6LBSGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3071.4
2.5°	3063.4
5°	3047.5
7.5°	3023.8
10°	2992.0
12.5°	2936.4
15°	2880.9
17.5°	2817.4
20°	2746.0
22.5°	2658.6
25°	2571.4
27.5°	2484.0
30°	2372.9
32.5°	2269.8
35°	2158.6
37.5°	2047.5
40°	1936.5
42.5°	1817.4
45°	1682.5
47.5°	1547.6
50°	1404.8
52.5°	1253.9
55°	1111.1
57.5°	968.2
60°	817.4
62.5°	674.6
65°	547.6
67.5°	420.6
70°	309.5
72.5°	206.4
75°	127.0
77.5°	55.5
80°	15.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)