

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204277

Luminaire Tested: **LE_6B20D010 EC6B10209730 6LBSWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204277
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B20D010 EC6B10209730 6LBSWH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1991.4 lumens
Efficiency: N/A
Efficacy: 95.7 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204277

CATALOG NUMBER: LE_6B20D010 EC6B10209730 6LBSWH1

Luminous Intensity Polar Plot





TEST NUMBER: P204277

CATALOG NUMBER: LE_6B20D010 EC6B10209730 6LBSWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89																											
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77																											
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67																											
4	88	77	70	64	86	76	69	63	74	68	63	72	66	62	69	65	61	59																											
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52																											
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47																											
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42																											
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38																											
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35																											
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32																											

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204277

CATALOG NUMBER: LE_6B20D010 EC6B10209730 6LBSWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.5	5.5
10°-20°	283.5	14.2
20°-30°	370.8	18.6
30°-40°	392.7	19.7
40°-50°	366.2	18.4
50°-60°	277.4	13.9
60°-70°	150.2	7.5
70°-80°	40.3	2.0
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	763.9	38.4
0°-40°	1156.6	58.1
0°-60°	1800.2	90.4
0°-90°	1991.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1991.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1188	
5°	1170	110
15°	1013	284
25°	806	371
35°	628	393
45°	477	366
55°	312	277
65°	150	150
75°	35	40
85°	0	1
90°	0	



TEST NUMBER: P204277

CATALOG NUMBER: LE_6B20D010 EC6B10209730 6LBSWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1187.6
2.5°	1183.2
5°	1170.2
7.5°	1141.9
10°	1104.9
12.5°	1061.2
15°	1013.2
17.5°	958.9
20°	910.9
22.5°	856.4
25°	806.2
27.5°	756.1
30°	708.2
32.5°	666.9
35°	627.6
37.5°	588.4
40°	551.4
42.5°	514.2
45°	477.2
47.5°	435.9
50°	394.4
52.5°	353.0
55°	311.6
57.5°	268.0
60°	226.6
62.5°	187.4
65°	150.4
67.5°	115.5
70°	85.0
72.5°	58.9
75°	34.9
77.5°	15.2
80°	4.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)