

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204204

Luminaire Tested: **LE_6B50D010R EC6B30508040 6LBSH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204204
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B50D010R EC6B30508040 6LBSH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7207.6 lumens
Efficiency: N/A
Efficacy: 122.6 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204204

CATALOG NUMBER: LE_6B50D010R EC6B30508040 6LBSH1

Luminous Intensity Polar Plot





TEST NUMBER: P204204

CATALOG NUMBER: LE_6B50D010R EC6B30508040 6LBSH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88		
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77		
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67		
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58		
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51		
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46		
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41		
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37		
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34		
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204204

CATALOG NUMBER: LE_6B50D010R EC6B30508040 6LBSH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	353.1	4.9
10°-20°	959.7	13.3
20°-30°	1332.8	18.5
30°-40°	1454.4	20.2
40°-50°	1356.7	18.8
50°-60°	1029.8	14.3
60°-70°	563.9	7.8
70°-80°	155.2	2.2
80°-90°	2.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2645.5	36.7
0°-40°	4099.9	56.9
0°-60°	6486.4	90.0
0°-90°	7207.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7207.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3770	
5°	3738	353
15°	3420	960
25°	2897	1333
35°	2325	1454
45°	1762	1357
55°	1151	1030
65°	564	564
75°	135	155
85°	0	2
90°	0	



TEST NUMBER: P204204

CATALOG NUMBER: LE_6B50D010R EC6B30508040 6LBSH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3769.5
2.5°	3769.5
5°	3737.8
7.5°	3690.1
10°	3618.8
12.5°	3523.5
15°	3420.4
17.5°	3293.4
20°	3174.4
22.5°	3031.5
25°	2896.6
27.5°	2761.6
30°	2610.9
32.5°	2468.0
35°	2325.2
37.5°	2182.4
40°	2047.5
42.5°	1904.6
45°	1761.8
47.5°	1618.9
50°	1460.2
52.5°	1309.4
55°	1150.8
57.5°	999.9
60°	849.1
62.5°	698.4
65°	563.5
67.5°	436.5
70°	325.4
72.5°	222.2
75°	134.9
77.5°	63.5
80°	15.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)