

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204933

Luminaire Tested: **LE_6B50D010R EC6B30509040 6LBCSMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204933
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B50D010R EC6B30509040 6LBCSMB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5380.3 lumens
Efficiency: N/A
Efficacy: 91.5 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204933

CATALOG NUMBER: LE_6B50D010R EC6B30509040 6LBSCMB1

Luminous Intensity Polar Plot





TEST NUMBER: P204933

CATALOG NUMBER: LE_6B50D010R EC6B30509040 6LBSCMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88			88
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75			75
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65			65
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56			56
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49			49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43			43
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39			39
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35			35
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31			31
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28			28

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204933

CATALOG NUMBER: LE_6B50D010R EC6B30509040 6LBSCMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.9	4.0
10°-20°	612.2	11.4
20°-30°	920.3	17.1
30°-40°	1091.9	20.3
40°-50°	1080.6	20.1
50°-60°	848.8	15.8
60°-70°	475.9	8.8
70°-80°	133.7	2.5
80°-90°	2.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1747.4	32.5
0°-40°	2839.3	52.8
0°-60°	4768.7	88.6
0°-90°	5380.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5380.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2272	
5°	2268	215
15°	2172	612
25°	1998	920
35°	1751	1092
45°	1408	1081
55°	957	849
65°	474	476
75°	116	134
85°	0	2
90°	0	



TEST NUMBER: P204933

CATALOG NUMBER: LE_6B50D010R EC6B30509040 6LBSCMB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2271.9
2.5°	2264.1
5°	2268.0
7.5°	2248.8
10°	2225.6
12.5°	2198.6
15°	2171.6
17.5°	2136.9
20°	2090.6
22.5°	2044.2
25°	1998.0
27.5°	1947.9
30°	1882.2
32.5°	1816.8
35°	1751.1
37.5°	1674.0
40°	1585.2
42.5°	1500.5
45°	1407.9
47.5°	1303.8
50°	1195.8
52.5°	1072.2
55°	956.6
57.5°	825.4
60°	702.0
62.5°	590.1
65°	474.4
67.5°	374.1
70°	277.8
72.5°	189.0
75°	115.8
77.5°	57.9
80°	15.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)