

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203546

Luminaire Tested: **LE\_6B20D010 EC6B10208035 6LBMMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203546  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B20D010 EC6B10208035 6LBMMW1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM  
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W  
DL3-21.8 6 W DLE-22.46 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2093.8 lumens  
Efficiency: N/A  
Efficacy: 100.7 lumens/watt  
Spacing Criteria (0/90/45): 1 / 1 / 0.97  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203546

CATALOG NUMBER: LE\_6B20D010 EC6B10208035 6LBMMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P203546

CATALOG NUMBER: LE\_6B20D010 EC6B10208035 6LBMMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58			
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53			
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48			
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41			
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203546

CATALOG NUMBER: LE\_6B20D010 EC6B10208035 6LBMMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	144.3	6.9
10°-20°	386.6	18.5
20°-30°	519.0	24.8
30°-40°	425.8	20.3
40°-50°	255.7	12.2
50°-60°	169.9	8.1
60°-70°	113.9	5.4
70°-80°	61.3	2.9
80°-90°	17.3	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1049.9	50.1
0°-40°	1475.7	70.5
0°-60°	1901.3	90.8
0°-90°	2093.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2093.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1562	
5°	1536	144
15°	1378	387
25°	1144	519
35°	676	426
45°	323	256
55°	188	170
65°	116	114
75°	58	61
85°	14	17
90°	0	



TEST NUMBER: P203546

CATALOG NUMBER: LE\_6B20D010 EC6B10208035 6LBMMW1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1562.2
2.5°	1550.8
5°	1536.2
7.5°	1504.5
10°	1467.0
12.5°	1420.8
15°	1377.5
17.5°	1325.5
20°	1273.5
22.5°	1215.8
25°	1143.5
27.5°	1056.9
30°	941.4
32.5°	811.5
35°	675.8
37.5°	560.2
40°	462.0
42.5°	384.1
45°	323.4
47.5°	274.4
50°	239.6
52.5°	210.8
55°	187.8
57.5°	167.5
60°	150.1
62.5°	130.0
65°	115.5
67.5°	98.1
70°	83.8
72.5°	69.2
75°	57.8
77.5°	46.2
80°	34.6
82.5°	26.0
85°	14.5
87.5°	5.8
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)