

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203649

Luminaire Tested: **LE\_6B20D010 EC6B10208035 6LBNH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203649  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B20D010 EC6B10208035 6LBNH1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W  
DL3-21.8 6 W DLE-22.46 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1642.1 lumens  
Efficiency: N/A  
Efficacy: 78.9 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203649

CATALOG NUMBER: LE\_6B20D010 EC6B10208035 6LBNH1

### Luminous Intensity Polar Plot





TEST NUMBER: P203649

CATALOG NUMBER: LE\_6B20D010 EC6B10208035 6LBNH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100																	
	1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93	93	93	93	93	93	93	93	93	93	93																	
	2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87	87	87	87	87	87	87	87	87	87	87																	
	3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81	81	81	81	81	81	81	81	81	81	81																	
	4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75	75	75	75	75	75	75	75	75	75	75																	
	5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70	70	70	70	70	70	70	70	70	70	70																	
	6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65	65	65	65	65	65	65	65	65	65	65																	
	7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61	61	61	61	61	61	61	61	61	61	61																	
	8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58	58	58	58	58	58	58	58	58	58	58																	
	9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54	54	54	54	54	54	54	54	54	54	54																	
	10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51	51	51	51	51	51	51	51	51	51	51																	

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203649

CATALOG NUMBER: LE\_6B20D010 EC6B10208035 6LBNH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	189.3	11.5
10°-20°	451.4	27.5
20°-30°	517.1	31.5
30°-40°	347.5	21.2
40°-50°	99.3	6.0
50°-60°	24.3	1.5
60°-70°	9.2	0.6
70°-80°	3.6	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1157.8	70.5
0°-40°	1505.3	91.7
0°-60°	1628.9	99.2
0°-90°	1642.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1642.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2105	
5°	2045	189
15°	1620	451
25°	1129	517
35°	554	347
45°	114	99
55°	27	24
65°	9	9
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P203649

CATALOG NUMBER: LE\_6B20D010 EC6B10208035 6LBNH1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2105.0
2.5°	2090.0
5°	2045.1
7.5°	1964.2
10°	1865.4
12.5°	1739.6
15°	1619.9
17.5°	1494.1
20°	1368.4
22.5°	1248.6
25°	1128.9
27.5°	1018.0
30°	889.2
32.5°	718.6
35°	554.0
37.5°	404.2
40°	278.5
42.5°	182.6
45°	113.8
47.5°	68.9
50°	41.9
52.5°	32.9
55°	27.0
57.5°	21.0
60°	15.0
62.5°	12.0
65°	9.0
67.5°	6.0
70°	6.0
72.5°	3.0
75°	3.0
77.5°	3.0
80°	3.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)