

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202871

Luminaire Tested: **LE\_6B50D010R EC6B30509040 6LBWWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P202871  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B50D010R EC6B30509040 6LBWWH1  
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH WHEAT TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5300.3 lumens  
Efficiency: N/A  
Efficacy: 90.1 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.18  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct

Input Watts (W): 58.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P202871  
CATALOG NUMBER: LE\_6B50D010R EC6B30509040 6LBWWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P202871

CATALOG NUMBER: LE\_6B50D010R EC6B30509040 6LBWWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68			
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	63	62			
6	82	71	64	59	80	71	64	59	69	63	59	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43			
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P202871

CATALOG NUMBER: LE\_6B50D010R EC6B30509040 6LBWWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	316.5	6.0
10°-20°	941.0	17.8
20°-30°	1416.5	26.7
30°-40°	1448.4	27.3
40°-50°	879.6	16.6
50°-60°	247.7	4.7
60°-70°	37.6	0.7
70°-80°	12.2	0.2
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2674.0	50.4
0°-40°	4122.3	77.8
0°-60°	5249.6	99.0
0°-90°	5300.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5300.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3292	
5°	3306	316
15°	3332	941
25°	3093	1417
35°	2348	1448
45°	1131	880
55°	246	248
65°	33	38
75°	13	12
85°	0	1
90°	0	



TEST NUMBER: P202871

CATALOG NUMBER: LE\_6B50D010R EC6B30509040 6LBWWH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3292.1
2.5°	3292.1
5°	3305.5
7.5°	3325.4
10°	3325.4
12.5°	3338.8
15°	3332.0
17.5°	3318.8
20°	3272.2
22.5°	3205.6
25°	3092.6
27.5°	2966.2
30°	2793.4
32.5°	2587.1
35°	2347.8
37.5°	2081.8
40°	1775.8
42.5°	1456.5
45°	1130.6
47.5°	838.0
50°	591.9
52.5°	399.0
55°	246.1
57.5°	146.4
60°	73.1
62.5°	46.5
65°	33.2
67.5°	26.6
70°	20.0
72.5°	13.2
75°	13.2
77.5°	6.6
80°	6.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)