

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203655

Luminaire Tested: **LE_6B20D010 EC6B10209035 6LBNH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203655
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B20D010 EC6B10209035 6LBNH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1388.2 lumens
Efficiency: N/A
Efficacy: 66.7 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203655

CATALOG NUMBER: LE_6B20D010 EC6B10209035 6LBNH1

Luminous Intensity Polar Plot





TEST NUMBER: P203655

CATALOG NUMBER: LE_6B20D010 EC6B10209035 6LBNH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93																											
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87																											
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81																											
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75																											
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70																											
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65																											
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61																											
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58																											
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54																											
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51																											

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203655

CATALOG NUMBER: LE_6B20D010 EC6B10209035 6LBNH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.0	11.5
10°-20°	381.6	27.5
20°-30°	437.2	31.5
30°-40°	293.7	21.2
40°-50°	83.9	6.0
50°-60°	20.6	1.5
60°-70°	7.8	0.6
70°-80°	3.0	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	978.9	70.5
0°-40°	1272.6	91.7
0°-60°	1377.1	99.2
0°-90°	1388.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1388.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1780	
5°	1729	160
15°	1370	382
25°	954	437
35°	468	294
45°	96	84
55°	23	21
65°	8	8
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P203655

CATALOG NUMBER: LE_6B20D010 EC6B10209035 6LBNH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1779.6
2.5°	1766.9
5°	1729.0
7.5°	1660.6
10°	1577.1
12.5°	1470.8
15°	1369.5
17.5°	1263.1
20°	1156.9
22.5°	1055.6
25°	954.4
27.5°	860.6
30°	751.9
32.5°	607.5
35°	468.2
37.5°	341.8
40°	235.4
42.5°	154.4
45°	96.2
47.5°	58.2
50°	35.5
52.5°	27.9
55°	22.8
57.5°	17.8
60°	12.6
62.5°	10.1
65°	7.6
67.5°	5.1
70°	5.1
72.5°	2.5
75°	2.5
77.5°	2.5
80°	2.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)