

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202728

Luminaire Tested: **LE_6B20D010 EC6B10209035 6LBWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202728
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B20D010 EC6B10209035 6LBWH1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1952.1 lumens
Efficiency: N/A
Efficacy: 93.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202728

CATALOG NUMBER: LE_6B20D010 EC6B10209035 6LBWH1

Luminous Intensity Polar Plot





TEST NUMBER: P202728

CATALOG NUMBER: LE_6B20D010 EC6B10209035 6LBWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202728

CATALOG NUMBER: LE_6B20D010 EC6B10209035 6LBWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.7	5.8
10°-20°	322.7	16.5
20°-30°	473.1	24.2
30°-40°	492.4	25.2
40°-50°	340.6	17.5
50°-60°	148.3	7.6
60°-70°	45.5	2.3
70°-80°	13.7	0.7
80°-90°	2.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	909.5	46.6
0°-40°	1401.9	71.8
0°-60°	1890.9	96.9
0°-90°	1952.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1952.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1204	
5°	1199	114
15°	1146	323
25°	1035	473
35°	797	492
45°	440	341
55°	159	148
65°	43	45
75°	13	14
85°	2	2
90°	0	



TEST NUMBER: P202728

CATALOG NUMBER: LE_6B20D010 EC6B10209035 6LBWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1204.0
2.5°	1206.6
5°	1199.0
7.5°	1188.9
10°	1176.2
12.5°	1163.6
15°	1145.9
17.5°	1123.1
20°	1097.9
22.5°	1070.0
25°	1034.6
27.5°	989.0
30°	930.9
32.5°	870.1
35°	796.8
37.5°	715.9
40°	622.2
42.5°	528.6
45°	440.1
47.5°	356.6
50°	283.2
52.5°	215.0
55°	159.4
57.5°	113.9
60°	78.4
62.5°	58.1
65°	43.0
67.5°	32.9
70°	22.8
72.5°	17.8
75°	12.6
77.5°	7.6
80°	5.0
82.5°	2.5
85°	2.5
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)