

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205137

Luminaire Tested: **LE\_6B50D010R EC6B30509050 6LBMLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205137  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B50D010R EC6B30509050 6LBML1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5210.1 lumens  
Efficiency: N/A  
Efficacy: 88.6 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 58.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205137

CATALOG NUMBER: LE\_6B50D010R EC6B30509050 6LBML11

### Luminous Intensity Polar Plot





TEST NUMBER: P205137

CATALOG NUMBER: LE\_6B50D010R EC6B30509050 6LBML11

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |  |  |  |  |  |  |  |  |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|--|--|--|--|--|--|--|--|
| RF  | 20  |     |     |     |     |     |     |     |     | 20  |     |     |     |     |     |     |     |     | 20 |    |    |    |    |    |    |    |    | 20 |    |   |  |  |  |  |  |  | 20 |  |  |  |  |  |  |  |  |   |  |  |  |  |  |  |  |  |
| RC  | 80  |     |     |     |     |     |     |     |     | 70  |     |     |     |     |     |     |     |     | 50 |    |    |    |    |    |    |    |    | 30 |    |   |  |  |  |  |  |  | 10 |  |  |  |  |  |  |  |  | 0 |  |  |  |  |  |  |  |  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |  |  |  |  |  |  |  |  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |  |  |  |  |  |  |  |  |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |  |  |  |  |  |  |  |  |
| 1   | 114 | 111 | 109 | 106 | 111 | 109 | 107 | 105 | 105 | 103 | 101 | 101 | 100 | 98  | 98  | 97  | 96  | 94  |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |  |  |  |  |  |  |  |  |
| 2   | 108 | 103 | 100 | 96  | 106 | 102 | 98  | 95  | 99  | 96  | 93  | 96  | 93  | 91  | 93  | 91  | 89  | 88  |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |  |  |  |  |  |  |  |  |
| 3   | 103 | 97  | 92  | 88  | 101 | 95  | 91  | 87  | 93  | 89  | 86  | 90  | 87  | 85  | 88  | 85  | 83  | 82  |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |  |  |  |  |  |  |  |  |
| 4   | 98  | 91  | 85  | 81  | 96  | 89  | 84  | 81  | 87  | 83  | 80  | 85  | 82  | 79  | 83  | 80  | 78  | 76  |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |  |  |  |  |  |  |  |  |
| 5   | 93  | 85  | 79  | 75  | 91  | 84  | 79  | 75  | 82  | 78  | 74  | 81  | 77  | 73  | 79  | 76  | 73  | 71  |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |  |  |  |  |  |  |  |  |
| 6   | 89  | 80  | 74  | 70  | 87  | 79  | 74  | 70  | 78  | 73  | 69  | 76  | 72  | 69  | 75  | 71  | 68  | 67  |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |  |  |  |  |  |  |  |  |
| 7   | 84  | 75  | 69  | 65  | 83  | 75  | 69  | 65  | 73  | 68  | 65  | 72  | 68  | 64  | 71  | 67  | 64  | 63  |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |  |  |  |  |  |  |  |  |
| 8   | 80  | 71  | 65  | 61  | 79  | 70  | 65  | 61  | 69  | 64  | 61  | 68  | 64  | 60  | 67  | 63  | 60  | 59  |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |  |  |  |  |  |  |  |  |
| 9   | 77  | 67  | 61  | 57  | 75  | 67  | 61  | 57  | 66  | 61  | 57  | 65  | 60  | 57  | 64  | 60  | 57  | 55  |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |  |  |  |  |  |  |  |  |
| 10  | 73  | 64  | 58  | 54  | 72  | 63  | 58  | 54  | 62  | 57  | 54  | 62  | 57  | 54  | 61  | 57  | 54  | 52  |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |  |  |  |  |  |  |  |  |

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205137

CATALOG NUMBER: LE\_6B50D010R EC6B30509050 6LBML11

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 600.7  | 11.5      |
| 10°-20°   | 1495.4 | 28.7      |
| 20°-30°   | 1738.4 | 33.4      |
| 30°-40°   | 1064.6 | 20.4      |
| 40°-50°   | 264.3  | 5.1       |
| 50°-60°   | 30.9   | 0.6       |
| 60°-70°   | 11.5   | 0.2       |
| 70°-80°   | 4.3    | 0.1       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 3834.5 | 73.6      |
| 0°-40°    | 4899.0 | 94.0      |
| 0°-60°    | 5194.2 | 99.7      |
| 0°-90°    | 5210.1 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 5210.1 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 6520 |      |
| 5°  | 6434 | 601  |
| 15° | 5367 | 1495 |
| 25° | 3847 | 1738 |
| 35° | 1667 | 1065 |
| 45° | 293  | 264  |
| 55° | 27   | 31   |
| 65° | 13   | 12   |
| 75° | 7    | 4    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P205137

CATALOG NUMBER: LE\_6B50D010R EC6B30509050 6LBML11

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 6520.4 |
| 2.5°  | 6513.6 |
| 5°    | 6433.6 |
| 7.5°  | 6260.2 |
| 10°   | 6027.0 |
| 12.5° | 5720.2 |
| 15°   | 5366.9 |
| 17.5° | 4986.9 |
| 20°   | 4613.5 |
| 22.5° | 4240.2 |
| 25°   | 3846.9 |
| 27.5° | 3393.5 |
| 30°   | 2873.5 |
| 32.5° | 2266.8 |
| 35°   | 1666.8 |
| 37.5° | 1173.4 |
| 40°   | 800.0  |
| 42.5° | 500.0  |
| 45°   | 293.4  |
| 47.5° | 166.6  |
| 50°   | 86.6   |
| 52.5° | 40.0   |
| 55°   | 26.6   |
| 57.5° | 20.0   |
| 60°   | 20.0   |
| 62.5° | 13.4   |
| 65°   | 13.4   |
| 67.5° | 6.6    |
| 70°   | 6.6    |
| 72.5° | 6.6    |
| 75°   | 6.6    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)