

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203650

Luminaire Tested: **LE_6B20D010 EC6B10208040 6LBNH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203650
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B20D010 EC6B10208040 6LBNH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1659.6 lumens
Efficiency: N/A
Efficacy: 79.8 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203650

CATALOG NUMBER: LE_6B20D010 EC6B10208040 6LBNH1

Luminous Intensity Polar Plot





TEST NUMBER: P203650

CATALOG NUMBER: LE_6B20D010 EC6B10208040 6LBNH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203650

CATALOG NUMBER: LE_6B20D010 EC6B10208040 6LBNH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	191.3	11.5
10°-20°	456.3	27.5
20°-30°	522.7	31.5
30°-40°	351.2	21.2
40°-50°	100.3	6.0
50°-60°	24.5	1.5
60°-70°	9.3	0.6
70°-80°	3.6	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1170.3	70.5
0°-40°	1521.5	91.7
0°-60°	1646.4	99.2
0°-90°	1659.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1659.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2128	
5°	2067	191
15°	1637	456
25°	1141	523
35°	560	351
45°	115	100
55°	27	25
65°	9	9
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P203650

CATALOG NUMBER: LE_6B20D010 EC6B10208040 6LBNH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2127.6
2.5°	2112.5
5°	2067.0
7.5°	1985.4
10°	1885.5
12.5°	1758.4
15°	1637.2
17.5°	1510.2
20°	1383.1
22.5°	1262.0
25°	1141.0
27.5°	1029.0
30°	898.9
32.5°	726.4
35°	559.9
37.5°	408.6
40°	281.5
42.5°	184.6
45°	115.0
47.5°	69.6
50°	42.4
52.5°	33.2
55°	27.2
57.5°	21.1
60°	15.1
62.5°	12.1
65°	9.1
67.5°	6.0
70°	6.0
72.5°	3.0
75°	3.0
77.5°	3.0
80°	3.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)