

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203753

Luminaire Tested: **LE_6B20D010 EC6B10208040 6LBNWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203753
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B20D010 EC6B10208040 6LBNWH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1777.6 lumens
Efficiency: N/A
Efficacy: 85.5 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.64
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203753

CATALOG NUMBER: LE_6B20D010 EC6B10208040 6LBNWH1

Luminous Intensity Polar Plot





TEST NUMBER: P203753

CATALOG NUMBER: LE_6B20D010 EC6B10208040 6LBNWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94		
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89		
3	104	98	93	90	102	97	92	89	94	91	88	92	89	86	89	87	85	83		
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	79		
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74		
6	91	82	77	73	89	82	76	73	80	76	72	79	75	72	78	74	71	70		
7	87	78	73	69	85	77	72	69	76	72	68	75	71	68	74	70	67	66		
8	83	74	69	65	82	74	68	65	73	68	65	72	67	64	71	67	64	63		
9	79	71	65	62	78	70	65	61	69	65	61	68	64	61	68	64	61	60		
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203753

CATALOG NUMBER: LE_6B20D010 EC6B10208040 6LBNWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	295.4	16.6
10°-20°	567.7	31.9
20°-30°	516.1	29.0
30°-40°	312.8	17.6
40°-50°	71.2	4.0
50°-60°	9.1	0.5
60°-70°	4.1	0.2
70°-80°	1.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1379.2	77.6
0°-40°	1692.0	95.2
0°-60°	1772.3	99.7
0°-90°	1777.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1777.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3490	
5°	3290	295
15°	2044	568
25°	1119	516
35°	496	313
45°	79	71
55°	9	9
65°	3	4
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P203753

CATALOG NUMBER: LE_6B20D010 EC6B10208040 6LBNWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3490.0
2.5°	3447.6
5°	3290.4
7.5°	3036.4
10°	2712.8
12.5°	2377.1
15°	2044.4
17.5°	1742.0
20°	1487.9
22.5°	1282.2
25°	1119.0
27.5°	973.8
30°	831.6
32.5°	665.4
35°	496.0
37.5°	347.8
40°	229.9
42.5°	142.1
45°	78.6
47.5°	36.2
50°	15.1
52.5°	12.1
55°	9.1
57.5°	9.1
60°	6.0
62.5°	6.0
65°	3.0
67.5°	3.0
70°	3.0
72.5°	3.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)