

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203704

Luminaire Tested: **LE_6B60D010R EC6B60709024 6LBNH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203704
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B60D010R EC6B60709024 6LBNH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3392.8 lumens
Efficiency: N/A
Efficacy: 54.3 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203704

CATALOG NUMBER: LE_6B60D010R EC6B60709024 6LBNH1

Luminous Intensity Polar Plot





TEST NUMBER: P203704

CATALOG NUMBER: LE_6B60D010R EC6B60709024 6LBNH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203704

CATALOG NUMBER: LE_6B60D010R EC6B60709024 6LBNH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	391.1	11.5
10°-20°	932.7	27.5
20°-30°	1068.6	31.5
30°-40°	718.0	21.2
40°-50°	205.1	6.0
50°-60°	50.1	1.5
60°-70°	19.1	0.6
70°-80°	7.3	0.2
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2392.4	70.5
0°-40°	3110.4	91.7
0°-60°	3365.6	99.2
0°-90°	3392.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3392.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4349	
5°	4226	391
15°	3347	933
25°	2332	1069
35°	1145	718
45°	235	205
55°	56	50
65°	18	19
75°	6	7
85°	0	1
90°	0	



TEST NUMBER: P203704

CATALOG NUMBER: LE_6B60D010R EC6B60709024 6LBNH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	4349.4
2.5°	4318.5
5°	4225.6
7.5°	4058.6
10°	3854.5
12.5°	3594.6
15°	3347.1
17.5°	3087.2
20°	2827.4
22.5°	2580.0
25°	2332.5
27.5°	2103.5
30°	1837.5
32.5°	1484.9
35°	1144.6
37.5°	835.2
40°	575.4
42.5°	377.4
45°	235.1
47.5°	142.2
50°	86.6
52.5°	68.0
55°	55.6
57.5°	43.2
60°	30.9
62.5°	24.8
65°	18.5
67.5°	12.4
70°	12.4
72.5°	6.1
75°	6.1
77.5°	6.1
80°	6.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)