

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205500

Luminaire Tested: **LE_6B20D010 EC6B10208050 6LBMGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205500
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B20D010 EC6B10208050 6LBMGPH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1471.7 lumens
Efficiency: N/A
Efficacy: 70.8 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205500

CATALOG NUMBER: LE_6B20D010 EC6B10208050 6LBMGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P205500

CATALOG NUMBER: LE_6B20D010 EC6B10208050 6LBMGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93			
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86			
3	102	95	90	85	99	93	89	85	91	87	83	88	85	82	86	83	81	79			
4	96	88	82	78	94	87	82	77	85	80	77	83	79	76	81	78	75	73			
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68			
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63			
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59			
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55			
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51			
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	53	49	48			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205500

CATALOG NUMBER: LE_6B20D010 EC6B10208050 6LBMGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.9	9.6
10°-20°	365.6	24.8
20°-30°	465.8	31.6
30°-40°	329.2	22.4
40°-50°	120.2	8.2
50°-60°	33.3	2.3
60°-70°	12.1	0.8
70°-80°	4.3	0.3
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	972.2	66.1
0°-40°	1301.4	88.4
0°-60°	1454.9	98.9
0°-90°	1471.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1471.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1534	
5°	1507	141
15°	1302	366
25°	1034	466
35°	523	329
45°	146	120
55°	36	33
65°	12	12
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P205500

CATALOG NUMBER: LE_6B20D010 EC6B10208050 6LBMGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1533.6
2.5°	1527.6
5°	1506.9
7.5°	1465.2
10°	1420.6
12.5°	1361.2
15°	1301.8
17.5°	1242.4
20°	1182.9
22.5°	1111.6
25°	1034.2
27.5°	927.2
30°	808.4
32.5°	665.8
35°	523.1
37.5°	398.2
40°	291.2
42.5°	211.0
45°	145.6
47.5°	98.1
50°	65.4
52.5°	44.6
55°	35.6
57.5°	26.8
60°	20.8
62.5°	14.9
65°	11.9
67.5°	8.9
70°	6.0
72.5°	6.0
75°	3.0
77.5°	3.0
80°	3.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)