

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203342

Luminaire Tested: **LE_6B20D010 EC6B10208050 6LBMWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203342
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B20D010 EC6B10208050 6LBMWH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2082.2 lumens
Efficiency: N/A
Efficacy: 100.1 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203342

CATALOG NUMBER: LE_6B20D010 EC6B10208050 6LBMWH1

Luminous Intensity Polar Plot





TEST NUMBER: P203342

CATALOG NUMBER: LE_6B20D010 EC6B10208050 6LBMWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94		
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	91	89	87		
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81		
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76		
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71		
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66		
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62		
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58		
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55		
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	52		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203342

CATALOG NUMBER: LE_6B20D010 EC6B10208050 6LBMWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	237.5	11.4
10°-20°	583.0	28.0
20°-30°	674.5	32.4
30°-40°	431.1	20.7
40°-50°	122.3	5.9
50°-60°	21.8	1.0
60°-70°	8.9	0.4
70°-80°	3.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1495.0	71.8
0°-40°	1926.1	92.5
0°-60°	2070.2	99.4
0°-90°	2082.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2082.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2598	
5°	2551	237
15°	2091	583
25°	1488	675
35°	680	431
45°	142	122
55°	20	22
65°	9	9
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P203342

CATALOG NUMBER: LE_6B20D010 EC6B10208050 6LBMWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	2597.5
2.5°	2594.6
5°	2551.2
7.5°	2473.0
10°	2363.0
12.5°	2235.5
15°	2090.8
17.5°	1940.2
20°	1792.5
22.5°	1647.8
25°	1488.5
27.5°	1314.8
30°	1120.6
32.5°	903.5
35°	680.5
37.5°	492.2
40°	341.8
42.5°	225.9
45°	141.9
47.5°	84.0
50°	49.2
52.5°	29.0
55°	20.2
57.5°	17.4
60°	14.5
62.5°	11.6
65°	8.6
67.5°	5.8
70°	5.8
72.5°	2.9
75°	2.9
77.5°	2.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)