

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202777

Luminaire Tested: **LE_6B60D010R EC6B60709024 6LBWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202777
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B60D010R EC6B60709024 6LBWH1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4771.1 lumens
Efficiency: N/A
Efficacy: 76.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202777

CATALOG NUMBER: LE_6B60D010R EC6B60709024 6LBWH1

Luminous Intensity Polar Plot





TEST NUMBER: P202777

CATALOG NUMBER: LE_6B60D010R EC6B60709024 6LBWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202777

CATALOG NUMBER: LE_6B60D010R EC6B60709024 6LBWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	277.9	5.8
10°-20°	788.7	16.5
20°-30°	1156.3	24.2
30°-40°	1203.5	25.2
40°-50°	832.7	17.5
50°-60°	362.5	7.6
60°-70°	111.2	2.3
70°-80°	33.3	0.7
80°-90°	5.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2223.0	46.6
0°-40°	3426.4	71.8
0°-60°	4621.6	96.9
0°-90°	4771.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4771.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2943	
5°	2930	278
15°	2801	789
25°	2529	1156
35°	1947	1203
45°	1076	833
55°	390	362
65°	105	111
75°	31	33
85°	6	5
90°	0	



TEST NUMBER: P202777

CATALOG NUMBER: LE_6B60D010R EC6B60709024 6LBWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2942.8
2.5°	2949.0
5°	2930.4
7.5°	2905.8
10°	2874.8
12.5°	2843.9
15°	2800.6
17.5°	2745.0
20°	2683.1
22.5°	2615.1
25°	2528.6
27.5°	2417.2
30°	2275.1
32.5°	2126.8
35°	1947.4
37.5°	1749.6
40°	1520.9
42.5°	1292.1
45°	1075.8
47.5°	871.8
50°	692.4
52.5°	525.5
55°	389.5
57.5°	278.2
60°	191.6
62.5°	142.2
65°	105.1
67.5°	80.4
70°	55.6
72.5°	43.2
75°	30.9
77.5°	18.5
80°	12.4
82.5°	6.1
85°	6.1
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)