

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204372

Luminaire Tested: **LE_6B20D010 EC6B10208050 6LBSGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204372
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B20D010 EC6B10208050 6LBSGPH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2520.3 lumens
Efficiency: N/A
Efficacy: 121.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204372

CATALOG NUMBER: LE_6B20D010 EC6B10208050 6LBSGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P204372

CATALOG NUMBER: LE_6B20D010 EC6B10208050 6LBSGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76			
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66			
4	87	76	68	62	85	75	67	62	72	66	61	70	65	60	68	63	59	57			
5	80	68	60	54	78	67	60	54	65	59	53	63	58	53	62	56	52	50			
6	74	62	54	48	73	61	53	48	59	52	47	58	52	47	56	51	47	45			
7	69	57	48	43	68	56	48	43	54	47	42	53	47	42	52	46	42	40			
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36			
9	60	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	32			
10	57	44	37	32	56	44	36	32	43	36	31	42	36	31	41	35	31	30			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204372

CATALOG NUMBER: LE_6B20D010 EC6B10208050 6LBSGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.2	4.4
10°-20°	309.4	12.3
20°-30°	451.2	17.9
30°-40°	514.6	20.4
40°-50°	493.6	19.6
50°-60°	378.0	15.0
60°-70°	207.4	8.2
70°-80°	55.1	2.2
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	870.8	34.6
0°-40°	1385.3	55.0
0°-60°	2256.9	89.5
0°-90°	2520.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2520.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1171	
5°	1162	110
15°	1098	309
25°	980	451
35°	823	515
45°	641	494
55°	424	378
65°	209	207
75°	48	55
85°	0	1
90°	0	



TEST NUMBER: P204372

CATALOG NUMBER: LE_6B20D010 EC6B10208050 6LBSGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1170.6
2.5°	1167.5
5°	1161.5
7.5°	1152.4
10°	1140.4
12.5°	1119.1
15°	1098.0
17.5°	1073.8
20°	1046.5
22.5°	1013.2
25°	980.0
27.5°	946.8
30°	904.4
32.5°	865.1
35°	822.8
37.5°	780.4
40°	738.0
42.5°	692.6
45°	641.2
47.5°	589.9
50°	535.4
52.5°	477.9
55°	423.5
57.5°	369.0
60°	311.5
62.5°	257.1
65°	208.8
67.5°	160.2
70°	118.0
72.5°	78.6
75°	48.4
77.5°	21.1
80°	6.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)