

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205140

Luminaire Tested: **LE_6B60D010R EC6B60708027 6LBMLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205140
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B60D010R EC6B60708027 6LBML1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6389.5 lumens
Efficiency: N/A
Efficacy: 102.2 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205140

CATALOG NUMBER: LE_6B60D010R EC6B60708027 6LBML11

Luminous Intensity Polar Plot





TEST NUMBER: P205140

CATALOG NUMBER: LE_6B60D010R EC6B60708027 6LBML11

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94			
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82			
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76			
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63			
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205140

CATALOG NUMBER: LE_6B60D010R EC6B60708027 6LBML11

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	736.6	11.5
10°-20°	1834.0	28.7
20°-30°	2131.9	33.4
30°-40°	1305.5	20.4
40°-50°	324.2	5.1
50°-60°	37.9	0.6
60°-70°	14.1	0.2
70°-80°	5.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4702.5	73.6
0°-40°	6008.0	94.0
0°-60°	6370.1	99.7
0°-90°	6389.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6389.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7996	
5°	7890	737
15°	6582	1834
25°	4718	2132
35°	2044	1306
45°	360	324
55°	33	38
65°	16	14
75°	8	5
85°	0	0
90°	0	



TEST NUMBER: P205140

CATALOG NUMBER: LE_6B60D010R EC6B60708027 6LBML11

CANDELA DISTRIBUTION (FULL):

	0°
0°	7996.4
2.5°	7988.1
5°	7890.0
7.5°	7677.5
10°	7391.2
12.5°	7015.2
15°	6581.9
17.5°	6115.8
20°	5658.0
22.5°	5200.1
25°	4717.6
27.5°	4161.8
30°	3524.0
32.5°	2779.9
35°	2044.0
37.5°	1439.0
40°	981.1
42.5°	613.2
45°	359.8
47.5°	204.4
50°	106.2
52.5°	49.0
55°	32.8
57.5°	24.5
60°	24.5
62.5°	16.4
65°	16.4
67.5°	8.1
70°	8.1
72.5°	8.1
75°	8.1
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)