

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203596

Luminaire Tested: **LE_6B60D010R EC6B60708027 6LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203596
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B60D010R EC6B60708027 6LBMMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5726.9 lumens
Efficiency: N/A
Efficacy: 91.6 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203596

CATALOG NUMBER: LE_6B60D010R EC6B60708027 6LBMMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203596

CATALOG NUMBER: LE_6B60D010R EC6B60708027 6LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58			
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53			
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48			
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41			
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203596

CATALOG NUMBER: LE_6B60D010R EC6B60708027 6LBMMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	394.7	6.9
10°-20°	1057.3	18.5
20°-30°	1419.7	24.8
30°-40°	1164.6	20.3
40°-50°	699.3	12.2
50°-60°	464.7	8.1
60°-70°	311.5	5.4
70°-80°	167.7	2.9
80°-90°	47.3	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2871.8	50.1
0°-40°	4036.4	70.5
0°-60°	5200.5	90.8
0°-90°	5726.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5726.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4273	
5°	4202	395
15°	3768	1057
25°	3128	1420
35°	1848	1165
45°	885	699
55°	513	465
65°	316	312
75°	158	168
85°	40	47
90°	0	



TEST NUMBER: P203596

CATALOG NUMBER: LE_6B60D010R EC6B60708027 6LBMMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	4273.2
2.5°	4241.6
5°	4202.1
7.5°	4115.2
10°	4012.5
12.5°	3886.1
15°	3767.6
17.5°	3625.5
20°	3483.4
22.5°	3325.4
25°	3127.9
27.5°	2890.9
30°	2575.0
32.5°	2219.5
35°	1848.2
37.5°	1532.4
40°	1263.8
42.5°	1050.5
45°	884.6
47.5°	750.4
50°	655.6
52.5°	576.6
55°	513.4
57.5°	458.1
60°	410.8
62.5°	355.5
65°	316.0
67.5°	268.5
70°	229.1
72.5°	189.6
75°	158.0
77.5°	126.4
80°	94.8
82.5°	71.1
85°	39.5
87.5°	15.8
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)