

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P252788

Luminaire Tested: **LE\_6B20D010 EC6B10209050 6LBBA1MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P252788  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1712-453-2)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B20D010 EC6B10209050 6LBBA1MW  
Description: PORTFOLIO 6 INCH BAFFLE RECESSED DOWNLIGHT, WITH MATTE WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2825.0 lumens  
Efficiency: N/A  
Efficacy: 135.8 lumens/watt  
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1  
Luminous Opening: Circular (Dia: 0.46' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P252788

CATALOG NUMBER: LE\_6B20D010 EC6B10209050 6LBBA1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P252788

CATALOG NUMBER: LE\_6B20D010 EC6B10209050 6LBBA1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88			
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78			
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69			
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	68	64	62			
5	84	73	65	60	82	72	65	60	70	64	59	68	63	58	66	62	58	56			
6	78	67	60	54	77	66	59	54	65	58	54	63	57	53	62	57	53	51			
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	47			
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	53	48	44	43			
9	65	54	46	42	64	53	46	42	52	46	41	51	45	41	50	45	41	39			
10	62	50	43	39	61	50	43	39	49	43	38	48	42	38	47	42	38	37			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	126410
5°	125249
10°	122491
15°	118604
20°	113806
25°	106840
30°	92449
35°	71990
40°	54710
45°	42645
50°	35371
55°	31746
60°	28902
65°	26676
70°	24511
75°	22712
80°	20514
85°	18789



TEST NUMBER: P252788

CATALOG NUMBER: LE\_6B20D010 EC6B10209050 6LBBA1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	180.5	6.4
10°-20°	493.4	17.5
20°-30°	671.9	23.8
30°-40°	568.6	20.1
40°-50°	364.8	12.9
50°-60°	251.0	8.9
60°-70°	171.5	6.1
70°-80°	95.4	3.4
80°-90°	27.9	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1345.8	47.6
0°-40°	1914.5	67.8
0°-60°	2530.2	89.6
0°-90°	2825.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2825.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1938	
5°	1912	181
15°	1756	493
25°	1484	672
35°	904	569
45°	462	365
55°	279	251
65°	173	171
75°	90	95
85°	25	28
90°	0	



TEST NUMBER: P252788

CATALOG NUMBER: LE\_6B20D010 EC6B10209050 6LBBA1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1937.6
2.5°	1930.2
5°	1912.5
7.5°	1884.5
10°	1849.0
12.5°	1804.8
15°	1756.0
17.5°	1699.9
20°	1639.2
22.5°	1571.4
25°	1484.2
27.5°	1366.1
30°	1227.2
32.5°	1067.8
35°	903.9
37.5°	760.6
40°	642.4
42.5°	543.5
45°	462.2
47.5°	398.8
50°	348.5
52.5°	310.1
55°	279.1
57.5°	249.6
60°	221.5
62.5°	196.4
65°	172.8
67.5°	149.1
70°	128.5
72.5°	107.8
75°	90.1
77.5°	72.4
80°	54.6
82.5°	39.9
85°	25.1
87.5°	10.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)