

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204731

Luminaire Tested: **LE\_6B60D010R EC6B60708027 6LBPSMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204731  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B60D010R EC6B60708027 6LBPSMW1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7755.7 lumens  
Efficiency: N/A  
Efficacy: 124.1 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 62.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204731

CATALOG NUMBER: LE\_6B60D010R EC6B60708027 6LBPSMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P204731

CATALOG NUMBER: LE\_6B60D010R EC6B60708027 6LBPSMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																																				
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74																																				
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63																																				
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54																																				
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47																																				
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42																																				
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37																																				
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33																																				
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30																																				
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27																																				

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204731

CATALOG NUMBER: LE\_6B60D010R EC6B60708027 6LBPSMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	296.1	3.8
10°-20°	844.0	10.9
20°-30°	1271.0	16.4
30°-40°	1512.4	19.5
40°-50°	1509.7	19.5
50°-60°	1227.7	15.8
60°-70°	755.3	9.7
70°-80°	292.6	3.8
80°-90°	46.9	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2411.1	31.1
0°-40°	3923.5	50.6
0°-60°	6660.9	85.9
0°-90°	7755.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7755.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3125	
5°	3116	296
15°	2996	844
25°	2766	1271
35°	2422	1512
45°	1962	1510
55°	1374	1228
65°	758	755
75°	266	293
85°	37	47
90°	0	



TEST NUMBER: P204731

CATALOG NUMBER: LE\_6B60D010R EC6B60708027 6LBPSMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3124.8
2.5°	3129.4
5°	3115.6
7.5°	3097.2
10°	3074.2
12.5°	3032.9
15°	2996.1
17.5°	2941.0
20°	2881.2
22.5°	2826.1
25°	2766.4
27.5°	2683.6
30°	2600.9
32.5°	2522.9
35°	2421.8
37.5°	2311.4
40°	2210.4
42.5°	2086.2
45°	1962.2
47.5°	1828.9
50°	1686.5
52.5°	1539.4
55°	1374.0
57.5°	1213.1
60°	1056.9
62.5°	905.2
65°	758.2
67.5°	620.4
70°	491.8
72.5°	372.2
75°	266.5
77.5°	174.6
80°	105.8
82.5°	64.4
85°	36.8
87.5°	18.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)