

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204792

Luminaire Tested: **LE_6B20D010 EC6B10209050 6LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204792
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B20D010 EC6B10209050 6LBCSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2438.5 lumens
Efficiency: N/A
Efficacy: 117.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204792

CATALOG NUMBER: LE_6B20D010 EC6B10209050 6LBCSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204792

CATALOG NUMBER: LE_6B20D010 EC6B10209050 6LBCSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87	87	87	87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74	74	74	74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63	63	63	63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55	55	55	55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48	48	48	48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42	42	42	42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37	37	37	37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33	33	33	33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30	30	30	30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27	27	27	27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204792

CATALOG NUMBER: LE_6B20D010 EC6B10209050 6LBCSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.4	3.9
10°-20°	268.6	11.0
20°-30°	404.1	16.6
30°-40°	478.9	19.6
40°-50°	476.6	19.5
50°-60°	384.2	15.8
60°-70°	232.4	9.5
70°-80°	86.3	3.5
80°-90°	12.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	767.1	31.5
0°-40°	1246.1	51.1
0°-60°	2106.9	86.4
0°-90°	2438.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2438.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	996	
5°	992	94
15°	952	269
25°	878	404
35°	767	479
45°	621	477
55°	428	384
65°	234	232
75°	78	86
85°	10	13
90°	0	



TEST NUMBER: P204792

CATALOG NUMBER: LE_6B20D010 EC6B10209050 6LBCSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	996.0
2.5°	996.0
5°	991.5
7.5°	988.5
10°	979.8
12.5°	964.9
15°	951.6
17.5°	936.9
20°	919.1
22.5°	901.4
25°	877.8
27.5°	852.6
30°	824.5
32.5°	798.0
35°	766.9
37.5°	734.4
40°	696.0
42.5°	659.0
45°	620.6
47.5°	577.8
50°	530.5
52.5°	481.8
55°	428.5
57.5°	381.2
60°	328.0
62.5°	280.8
65°	233.5
67.5°	189.1
70°	147.8
72.5°	110.9
75°	78.4
77.5°	50.2
80°	29.5
82.5°	17.8
85°	10.4
87.5°	4.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)