

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202978

Luminaire Tested: **LE\_6B60D010R EC6B60708027 6LBWGPH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P202978  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B60D010R EC6B60708027 6LBWGPH1  
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTIONWITH GRAPHITE HAZE TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4753.3 lumens  
Efficiency: N/A  
Efficacy: 76.1 lumens/watt  
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.11  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 62.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P202978

CATALOG NUMBER: LE\_6B60D010R EC6B60708027 6LBWGP1

### Luminous Intensity Polar Plot





TEST NUMBER: P202978

CATALOG NUMBER: LE\_6B60D010R EC6B60708027 6LBWGPH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82			
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74			
4	93	84	77	72	91	82	76	72	80	75	71	78	74	70	76	72	69	67			
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61			
6	81	71	64	59	80	70	63	59	68	62	58	67	62	58	65	61	57	56			
7	76	65	58	53	75	65	58	53	63	57	53	62	57	53	61	56	52	51			
8	72	61	54	49	70	60	53	49	59	53	49	58	52	48	57	52	48	47			
9	68	57	50	45	66	56	49	45	55	49	45	54	48	45	53	48	44	43			
10	64	53	46	42	63	52	46	42	51	45	41	51	45	41	50	45	41	40			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P202978

CATALOG NUMBER: LE\_6B60D010R EC6B60708027 6LBWGPH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	304.4	6.4
10°-20°	853.5	18.0
20°-30°	1221.0	25.7
30°-40°	1217.1	25.6
40°-50°	775.2	16.3
50°-60°	285.8	6.0
60°-70°	71.5	1.5
70°-80°	21.5	0.5
80°-90°	3.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2378.9	50.0
0°-40°	3595.9	75.7
0°-60°	4657.0	98.0
0°-90°	4753.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4753.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3231	
5°	3214	304
15°	3034	853
25°	2666	1221
35°	1979	1217
45°	998	775
55°	303	286
65°	65	72
75°	16	22
85°	0	3
90°	0	



TEST NUMBER: P202978

CATALOG NUMBER: LE\_6B60D010R EC6B60708027 6LBWGPH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3230.6
2.5°	3230.6
5°	3214.2
7.5°	3181.6
10°	3140.6
12.5°	3091.6
15°	3034.4
17.5°	2960.8
20°	2879.0
22.5°	2789.0
25°	2666.2
27.5°	2535.4
30°	2363.6
32.5°	2183.8
35°	1979.2
37.5°	1733.9
40°	1480.4
42.5°	1235.0
45°	997.9
47.5°	785.1
50°	588.9
52.5°	433.5
55°	302.6
57.5°	196.2
60°	130.9
62.5°	90.0
65°	65.4
67.5°	49.1
70°	40.9
72.5°	24.5
75°	16.4
77.5°	16.4
80°	8.1
82.5°	8.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)