

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205099

Luminaire Tested: **LE_6B20D010 EC6B10209050 6LBMLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205099
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B20D010 EC6B10209050 6LBML1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1986.4 lumens
Efficiency: N/A
Efficacy: 95.5 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205099

CATALOG NUMBER: LE_6B20D010 EC6B10209050 6LBMLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205099

CATALOG NUMBER: LE_6B20D010 EC6B10209050 6LBMLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94																			
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88																			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82																			
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76																			
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71																			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67																			
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63																			
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205099

CATALOG NUMBER: LE_6B20D010 EC6B10209050 6LBMLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	229.0	11.5
10°-20°	570.2	28.7
20°-30°	662.8	33.4
30°-40°	405.9	20.4
40°-50°	100.8	5.1
50°-60°	11.7	0.6
60°-70°	4.4	0.2
70°-80°	1.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1462.0	73.6
0°-40°	1867.9	94.0
0°-60°	1980.4	99.7
0°-90°	1986.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1986.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2486	
5°	2453	229
15°	2046	570
25°	1467	663
35°	636	406
45°	112	101
55°	10	12
65°	5	4
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P205099

CATALOG NUMBER: LE_6B20D010 EC6B10209050 6LBMLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2486.1
2.5°	2483.5
5°	2453.0
7.5°	2387.0
10°	2298.0
12.5°	2181.0
15°	2046.2
17.5°	1901.4
20°	1759.1
22.5°	1616.8
25°	1466.8
27.5°	1293.9
30°	1095.6
32.5°	864.2
35°	635.5
37.5°	447.4
40°	305.0
42.5°	190.6
45°	111.9
47.5°	63.5
50°	33.0
52.5°	15.2
55°	10.1
57.5°	7.6
60°	7.6
62.5°	5.1
65°	5.1
67.5°	2.5
70°	2.5
72.5°	2.5
75°	2.5
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)