

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204180

Luminaire Tested: **LE\_6B30D010 EC6B30509024 6LBSH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204180  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B30D010 EC6B30509024 6LBSH1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W  
DL3-29.67 W DLE-29.73 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2779.8 lumens  
Efficiency: N/A  
Efficacy: 99.3 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204180

CATALOG NUMBER: LE\_6B30D010 EC6B30509024 6LBSH1

### Luminous Intensity Polar Plot





TEST NUMBER: P204180

CATALOG NUMBER: LE\_6B30D010 EC6B30509024 6LBSH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88		
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77		
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67		
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58		
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51		
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46		
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41		
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37		
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34		
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31		

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204180

CATALOG NUMBER: LE\_6B30D010 EC6B30509024 6LBSH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	136.2	4.9
10°-20°	370.1	13.3
20°-30°	514.0	18.5
30°-40°	560.9	20.2
40°-50°	523.3	18.8
50°-60°	397.1	14.3
60°-70°	217.5	7.8
70°-80°	59.9	2.2
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1020.3	36.7
0°-40°	1581.2	56.9
0°-60°	2501.6	90.0
0°-90°	2779.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2779.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1454	
5°	1442	136
15°	1319	370
25°	1117	514
35°	897	561
45°	680	523
55°	444	397
65°	217	217
75°	52	60
85°	0	1
90°	0	



TEST NUMBER: P204180

CATALOG NUMBER: LE\_6B30D010 EC6B30509024 6LBSH1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1453.9
2.5°	1453.9
5°	1441.6
7.5°	1423.2
10°	1395.6
12.5°	1359.0
15°	1319.1
17.5°	1270.1
20°	1224.2
22.5°	1169.1
25°	1117.1
27.5°	1065.1
30°	1007.0
32.5°	951.9
35°	896.8
37.5°	841.6
40°	789.6
42.5°	734.6
45°	679.5
47.5°	624.4
50°	563.1
52.5°	505.0
55°	443.8
57.5°	385.6
60°	327.5
62.5°	269.4
65°	217.2
67.5°	168.4
70°	125.5
72.5°	85.8
75°	52.0
77.5°	24.5
80°	6.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)