

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204943

Luminaire Tested: **LE\_6B60D010R EC6B60709027 6LBCSMB1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204943  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B60D010R EC6B60709027 6LBCSMB1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5690.5 lumens  
Efficiency: N/A  
Efficacy: 91.0 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 62.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204943

CATALOG NUMBER: LE\_6B60D010R EC6B60709027 6LBSCMB1

### Luminous Intensity Polar Plot





TEST NUMBER: P204943

CATALOG NUMBER: LE\_6B60D010R EC6B60709027 6LBSCMB1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88			88
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75			75
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65			65
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56			56
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49			49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43			43
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39			39
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35			35
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31			31
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28			28

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204943

CATALOG NUMBER: LE\_6B60D010R EC6B60709027 6LBSCMB1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	227.3	4.0
10°-20°	647.5	11.4
20°-30°	973.3	17.1
30°-40°	1154.9	20.3
40°-50°	1142.9	20.1
50°-60°	897.7	15.8
60°-70°	503.3	8.8
70°-80°	141.4	2.5
80°-90°	2.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1848.1	32.5
0°-40°	3003.0	52.8
0°-60°	5043.6	88.6
0°-90°	5690.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5690.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2403	
5°	2399	227
15°	2297	647
25°	2113	973
35°	1852	1155
45°	1489	1143
55°	1012	898
65°	502	503
75°	122	141
85°	0	2
90°	0	



TEST NUMBER: P204943

CATALOG NUMBER: LE\_6B60D010R EC6B60709027 6LBSCMB1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2402.9
2.5°	2394.6
5°	2398.8
7.5°	2378.4
10°	2353.9
12.5°	2325.4
15°	2296.8
17.5°	2260.0
20°	2211.1
22.5°	2162.1
25°	2113.1
27.5°	2060.1
30°	1990.8
32.5°	1921.5
35°	1852.1
37.5°	1770.5
40°	1676.6
42.5°	1586.9
45°	1489.0
47.5°	1378.9
50°	1264.6
52.5°	1134.1
55°	1011.8
57.5°	873.0
60°	742.5
62.5°	624.1
65°	501.8
67.5°	395.8
70°	293.8
72.5°	199.9
75°	122.4
77.5°	61.2
80°	16.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)