

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202532

Luminaire Tested: **LE_6B30D010 EC6B30509024 6LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202532
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B30D010 EC6B30509024 6LBSWMH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2805.1 lumens
Efficiency: N/A
Efficacy: 100.2 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 1.1
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202532

CATALOG NUMBER: LE_6B30D010 EC6B30509024 6LBSWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P202532

CATALOG NUMBER: LE_6B30D010 EC6B30509024 6LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88				88
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	84	81	79	77				77
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67				67
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59				59
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52				52
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47				47
7	70	58	50	45	69	57	50	45	56	49	44	55	48	44	53	48	44	42				42
8	66	54	46	40	64	53	45	40	52	45	40	50	44	40	49	44	40	38				38
9	62	49	42	37	61	49	42	37	48	41	37	47	41	36	46	40	36	35				35
10	58	46	39	34	57	45	38	34	45	38	34	44	38	33	43	37	33	32				32

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202532

CATALOG NUMBER: LE_6B30D010 EC6B30509024 6LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.1	5.4
10°-20°	392.3	14.0
20°-30°	520.2	18.5
30°-40°	554.8	19.8
40°-50°	518.6	18.5
50°-60°	395.5	14.1
60°-70°	215.1	7.7
70°-80°	57.7	2.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1062.6	37.9
0°-40°	1617.4	57.7
0°-60°	2531.6	90.2
0°-90°	2805.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2805.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1622	
5°	1600	150
15°	1399	392
25°	1132	520
35°	887	555
45°	675	519
55°	445	395
65°	215	215
75°	50	58
85°	0	1
90°	0	



TEST NUMBER: P202532

CATALOG NUMBER: LE_6B30D010 EC6B30509024 6LBSWMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1622.1
2.5°	1616.9
5°	1599.8
7.5°	1563.6
10°	1522.4
12.5°	1464.0
15°	1398.8
17.5°	1333.4
20°	1263.0
22.5°	1196.0
25°	1132.4
27.5°	1065.4
30°	1001.8
32.5°	939.9
35°	886.6
37.5°	833.4
40°	778.4
42.5°	728.5
45°	675.2
47.5°	616.9
50°	561.9
52.5°	503.5
55°	445.0
57.5°	381.5
60°	323.0
62.5°	268.0
65°	214.8
67.5°	166.6
70°	122.0
72.5°	84.2
75°	49.9
77.5°	22.4
80°	5.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)