

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203150

Luminaire Tested: **LE_6B30D010 EC6B30509024 6LBWMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203150
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B30D010 EC6B30509024 6LBWMW1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2522.9 lumens
Efficiency: N/A
Efficacy: 90.1 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.15
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203150

CATALOG NUMBER: LE_6B30D010 EC6B30509024 6LBWMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203150

CATALOG NUMBER: LE_6B30D010 EC6B30509024 6LBWMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77			
3	95	86	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68			
4	89	78	71	65	86	77	70	65	75	69	64	72	67	63	70	66	62	60			
5	82	71	64	58	80	70	63	58	68	62	57	66	61	56	65	60	56	54			
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	49			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			
8	67	55	48	42	66	55	47	42	53	47	42	52	46	42	51	46	42	40			
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37			
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203150

CATALOG NUMBER: LE_6B30D010 EC6B30509024 6LBWMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.4	5.3
10°-20°	374.2	14.8
20°-30°	539.1	21.4
30°-40°	559.8	22.2
40°-50°	413.8	16.4
50°-60°	247.2	9.8
60°-70°	150.3	6.0
70°-80°	82.3	3.3
80°-90°	22.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1046.7	41.5
0°-40°	1606.5	63.7
0°-60°	2267.5	89.9
0°-90°	2522.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2522.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1417	
5°	1408	133
15°	1328	374
25°	1175	539
35°	903	560
45°	532	414
55°	269	247
65°	150	150
75°	76	82
85°	18	23
90°	0	



TEST NUMBER: P203150

CATALOG NUMBER: LE_6B30D010 EC6B30509024 6LBWMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1416.8
2.5°	1416.8
5°	1407.6
7.5°	1395.4
10°	1377.0
12.5°	1355.6
15°	1328.0
17.5°	1297.4
20°	1266.9
22.5°	1224.0
25°	1175.0
27.5°	1123.0
30°	1055.8
32.5°	988.4
35°	902.8
37.5°	814.0
40°	716.0
42.5°	621.1
45°	532.4
47.5°	452.9
50°	382.5
52.5°	321.2
55°	269.2
57.5°	229.5
60°	195.9
62.5°	171.4
65°	150.0
67.5°	131.6
70°	113.2
72.5°	94.9
75°	76.5
77.5°	61.2
80°	45.9
82.5°	33.6
85°	18.4
87.5°	9.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)