

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204795

Luminaire Tested: **LE\_6B30D010 EC6B30508027 6LBCSMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204795  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B30D010 EC6B30508027 6LBCSMW1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM  
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W  
DL3-29.67 W DLE-29.73 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3880.9 lumens  
Efficiency: N/A  
Efficacy: 138.6 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204795

CATALOG NUMBER: LE\_6B30D010 EC6B30508027 6LBCSMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P204795

CATALOG NUMBER: LE\_6B30D010 EC6B30508027 6LBCSMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87				87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74				74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63				63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55				55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48				48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42				42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37				37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33				33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30				30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27				27

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204795

CATALOG NUMBER: LE\_6B30D010 EC6B30508027 6LBCSMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	150.2	3.9
10°-20°	427.6	11.0
20°-30°	643.2	16.6
30°-40°	762.2	19.6
40°-50°	758.5	19.5
50°-60°	611.5	15.8
60°-70°	369.9	9.5
70°-80°	137.3	3.5
80°-90°	20.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1220.9	31.5
0°-40°	1983.2	51.1
0°-60°	3353.2	86.4
0°-90°	3880.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3880.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1585	
5°	1578	150
15°	1514	428
25°	1397	643
35°	1221	762
45°	988	759
55°	682	611
65°	372	370
75°	125	137
85°	16	20
90°	0	



TEST NUMBER: P204795

CATALOG NUMBER: LE\_6B30D010 EC6B30508027 6LBCSMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1585.1
2.5°	1585.1
5°	1578.0
7.5°	1573.4
10°	1559.2
12.5°	1535.8
15°	1514.5
17.5°	1491.0
20°	1462.8
22.5°	1434.6
25°	1397.0
27.5°	1357.0
30°	1312.2
32.5°	1270.0
35°	1220.6
37.5°	1168.9
40°	1107.6
42.5°	1048.9
45°	987.8
47.5°	919.5
50°	844.2
52.5°	766.6
55°	682.0
57.5°	606.8
60°	522.1
62.5°	446.9
65°	371.6
67.5°	301.0
70°	235.1
72.5°	176.4
75°	124.6
77.5°	80.0
80°	47.0
82.5°	28.2
85°	16.5
87.5°	7.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)