

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205102

Luminaire Tested: **LE_6B30D010 EC6B30508027 6LBMLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205102
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B30D010 EC6B30508027 6LBML1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3161.5 lumens
Efficiency: N/A
Efficacy: 112.9 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205102

CATALOG NUMBER: LE_6B30D010 EC6B30508027 6LBMLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205102

CATALOG NUMBER: LE_6B30D010 EC6B30508027 6LBMLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|----|----|----|----|---|--|--|--|----|--|--|--|--|--|--|--|--|---|--|--|--|--|--|--|--|--|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | | | | | | | | | |
| RC | 80 | | | | | | | | | 70 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 | | | | | | | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | | | | | | |
| RCR | 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | 1 | 114 | 111 | 109 | 106 | 111 | 109 | 107 | 105 | 105 | 103 | 101 | 101 | 100 | 98 | 98 | 97 | 96 | 94 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | 2 | 108 | 103 | 100 | 96 | 106 | 102 | 98 | 95 | 99 | 96 | 93 | 96 | 93 | 91 | 93 | 91 | 89 | 88 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | 3 | 103 | 97 | 92 | 88 | 101 | 95 | 91 | 87 | 93 | 89 | 86 | 90 | 87 | 85 | 88 | 85 | 83 | 82 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | 4 | 98 | 91 | 85 | 81 | 96 | 89 | 84 | 81 | 87 | 83 | 80 | 85 | 82 | 79 | 83 | 80 | 78 | 76 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | 5 | 93 | 85 | 79 | 75 | 91 | 84 | 79 | 75 | 82 | 78 | 74 | 81 | 77 | 73 | 79 | 76 | 73 | 71 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | 6 | 89 | 80 | 74 | 70 | 87 | 79 | 74 | 70 | 78 | 73 | 69 | 76 | 72 | 69 | 75 | 71 | 68 | 67 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | 7 | 84 | 75 | 69 | 65 | 83 | 75 | 69 | 65 | 73 | 68 | 65 | 72 | 68 | 64 | 71 | 67 | 64 | 63 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | 8 | 80 | 71 | 65 | 61 | 79 | 70 | 65 | 61 | 69 | 64 | 61 | 68 | 64 | 60 | 67 | 63 | 60 | 59 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | 9 | 77 | 67 | 61 | 57 | 75 | 67 | 61 | 57 | 66 | 61 | 57 | 65 | 60 | 57 | 64 | 60 | 57 | 55 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | 10 | 73 | 64 | 58 | 54 | 72 | 63 | 58 | 54 | 62 | 57 | 54 | 62 | 57 | 54 | 61 | 57 | 54 | 52 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205102

CATALOG NUMBER: LE_6B30D010 EC6B30508027 6LBMLI1

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 364.5 | 11.5 |
| 10°-20° | 907.5 | 28.7 |
| 20°-30° | 1054.9 | 33.4 |
| 30°-40° | 646.0 | 20.4 |
| 40°-50° | 160.4 | 5.1 |
| 50°-60° | 18.7 | 0.6 |
| 60°-70° | 7.0 | 0.2 |
| 70°-80° | 2.6 | 0.1 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 2326.9 | 73.6 |
| 0°-40° | 2972.9 | 94.0 |
| 0°-60° | 3152.0 | 99.7 |
| 0°-90° | 3161.5 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 3161.5 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 3957 | |
| 5° | 3904 | 364 |
| 15° | 3257 | 907 |
| 25° | 2334 | 1055 |
| 35° | 1011 | 646 |
| 45° | 178 | 160 |
| 55° | 16 | 19 |
| 65° | 8 | 7 |
| 75° | 4 | 3 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P205102

CATALOG NUMBER: LE_6B30D010 EC6B30508027 6LBMLI1

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 3956.8 |
| 2.5° | 3952.6 |
| 5° | 3904.1 |
| 7.5° | 3798.9 |
| 10° | 3657.4 |
| 12.5° | 3471.2 |
| 15° | 3256.8 |
| 17.5° | 3026.2 |
| 20° | 2799.6 |
| 22.5° | 2573.1 |
| 25° | 2334.4 |
| 27.5° | 2059.2 |
| 30° | 1743.8 |
| 32.5° | 1375.5 |
| 35° | 1011.4 |
| 37.5° | 712.0 |
| 40° | 485.5 |
| 42.5° | 303.4 |
| 45° | 178.0 |
| 47.5° | 101.1 |
| 50° | 52.6 |
| 52.5° | 24.2 |
| 55° | 16.1 |
| 57.5° | 12.1 |
| 60° | 12.1 |
| 62.5° | 8.1 |
| 65° | 8.1 |
| 67.5° | 4.0 |
| 70° | 4.0 |
| 72.5° | 4.0 |
| 75° | 4.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)