

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204431

Luminaire Tested: **LE_6B60D010R EC6B60709727 6LBSGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204431
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B60D010R EC6B60709727 6LBSGPH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5094.9 lumens
Efficiency: N/A
Efficacy: 81.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204431

CATALOG NUMBER: LE_6B60D010R EC6B60709727 6LBSGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P204431

CATALOG NUMBER: LE_6B60D010R EC6B60709727 6LBSGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	91	90	88			88																
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76			76																
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66			66																
4	87	76	68	62	85	75	67	62	72	66	61	70	65	60	68	63	59	57			57																
5	80	68	60	54	78	67	60	54	65	59	53	63	58	53	62	56	52	50			50																
6	74	62	54	48	73	61	53	48	59	52	47	58	52	47	56	51	47	45			45																
7	69	57	48	43	68	56	48	43	54	47	42	53	47	42	52	46	42	40			40																
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36			36																
9	60	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	32			32																
10	57	44	37	32	56	44	36	32	43	36	31	42	36	31	41	35	31	30			30																

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204431

CATALOG NUMBER: LE_6B60D010R EC6B60709727 6LBSGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	222.8	4.4
10°-20°	625.4	12.3
20°-30°	912.1	17.9
30°-40°	1040.1	20.4
40°-50°	997.8	19.6
50°-60°	764.2	15.0
60°-70°	419.4	8.2
70°-80°	111.5	2.2
80°-90°	1.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1760.3	34.6
0°-40°	2800.4	55.0
0°-60°	4562.3	89.5
0°-90°	5094.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5094.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2366	
5°	2348	223
15°	2220	625
25°	1981	912
35°	1663	1040
45°	1296	998
55°	856	764
65°	422	419
75°	98	112
85°	0	2
90°	0	



TEST NUMBER: P204431

CATALOG NUMBER: LE_6B60D010R EC6B60709727 6LBSGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2366.2
2.5°	2360.1
5°	2348.0
7.5°	2329.6
10°	2305.1
12.5°	2262.4
15°	2219.5
17.5°	2170.6
20°	2115.6
22.5°	2048.4
25°	1981.1
27.5°	1913.9
30°	1828.2
32.5°	1748.8
35°	1663.1
37.5°	1577.5
40°	1491.9
42.5°	1400.2
45°	1296.2
47.5°	1192.4
50°	1082.2
52.5°	966.1
55°	856.0
57.5°	746.0
60°	629.8
62.5°	519.8
65°	421.9
67.5°	324.1
70°	238.5
72.5°	159.0
75°	97.9
77.5°	42.8
80°	12.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)